

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286425

Luminaire Tested: P3AS05R259030D2WDE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286425
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259030D2WDE010 E3PHLD1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 401.0 lumens
Efficiency: N/A
Efficacy: 36.1 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286425
CATALOG NUMBER: P3AS05R259030D2WDE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1286425
 CATALOG NUMBER: P3AS05R259030D2WDE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80		
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72		
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65		
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59		
6	81	70	63	58	79	69	62	57	68	62	57	66	61	57	65	60	56	55		
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50		
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47		
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44		
10	65	54	47	43	64	53	47	43	52	47	43	52	46	43	51	46	42	41		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104619
5°	99317
10°	86015
15°	70034
20°	55328
25°	44132
30°	35778
35°	29125
40°	24131
45°	20343
50°	17228
55°	15139
60°	13288
65°	11571
70°	10194
75°	8557
80°	6314
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20343 cd/sqm



TEST NUMBER: P1286425

CATALOG NUMBER: P3AS05R259030D2WDE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.0	10.2
10°-20°	85.5	21.3
20°-30°	84.3	21.0
30°-40°	68.6	17.1
40°-50°	50.9	12.7
50°-60°	35.6	8.9
60°-70°	22.2	5.5
70°-80°	10.7	2.7
80°-90°	2.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	210.8	52.6
0°-40°	279.5	69.7
0°-60°	366.0	91.3
0°-90°	401.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	401.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	477	
5°	451	41
15°	308	86
25°	182	84
35°	109	69
45°	66	51
55°	40	36
65°	22	22
75°	10	11
85°	1	2
90°	0	



TEST NUMBER: P1286425
CATALOG NUMBER: P3AS05R259030D2WDE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	477.1
2.5°	470.7
5°	451.2
7.5°	421.6
10°	386.3
12.5°	347.4
15°	308.5
17.5°	270.3
20°	237.1
22.5°	208.3
25°	182.4
27.5°	160.0
30°	141.3
32.5°	124.0
35°	108.8
37.5°	95.9
40°	84.3
42.5°	74.2
45°	65.6
47.5°	57.7
50°	50.5
52.5°	44.7
55°	39.6
57.5°	34.6
60°	30.3
62.5°	25.9
65°	22.3
67.5°	18.7
70°	15.9
72.5°	13.0
75°	10.1
77.5°	7.2
80°	5.0
82.5°	2.9
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)