

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287113

Luminaire Tested: P3AS13R259030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1287113  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R259030D2WDE010 E3DLP1WMH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,  
E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 691.0 lumens  
Efficiency: N/A  
Efficacy: 34.4 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287113

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLP1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1287113

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 |  | 100 | 99  | 98  |  | 97  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  |  | 94  | 92  | 90  |  | 92  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 86  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 77  | 73  | 81  | 76  | 73  |  | 79  | 75  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 72  | 68  | 77  | 72  | 68  |  | 75  | 71  | 67  |  | 74  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 60  |  | 67  |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 61  | 57  | 65  | 60  | 57  |  | 65  | 60  | 57  |  | 64  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 57  | 54  |  | 62  | 57  | 54  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 250879 |
| 5°  | 240677 |
| 10° | 210840 |
| 15° | 169467 |
| 20° | 130211 |
| 25° | 98522  |
| 30° | 71201  |
| 35° | 47301  |
| 40° | 28682  |
| 45° | 16715  |
| 50° | 10644  |
| 55° | 8640   |
| 60° | 7543   |
| 65° | 6693   |
| 70° | 5514   |
| 75° | 5507   |
| 80° | 4041   |
| 85° | 5535   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16715 cd/sqm

TEST NUMBER: P1287113

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLP1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 99.5   | 14.4      |
| 10°-20°   | 206.4  | 29.9      |
| 20°-30°   | 186.7  | 27.0      |
| 30°-40°   | 112.2  | 16.2      |
| 40°-50°   | 44.6   | 6.4       |
| 50°-60°   | 20.5   | 3.0       |
| 60°-70°   | 12.5   | 1.8       |
| 70°-80°   | 6.7    | 1.0       |
| 80°-90°   | 1.9    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 492.7  | 71.3      |
| 0°-40°    | 604.8  | 87.5      |
| 0°-60°    | 669.9  | 96.9      |
| 0°-90°    | 691.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 691.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1144 |      |
| 5°  | 1093 | 100  |
| 15° | 746  | 206  |
| 25° | 407  | 187  |
| 35° | 177  | 112  |
| 45° | 54   | 45   |
| 55° | 23   | 21   |
| 65° | 13   | 13   |
| 75° | 6    | 7    |
| 85° | 2    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1287113

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1144.1 |
| 1°    | 1144.1 |
| 2°    | 1138.7 |
| 3°    | 1126.8 |
| 4°    | 1111.7 |
| 5°    | 1093.4 |
| 6°    | 1069.7 |
| 7°    | 1042.8 |
| 8°    | 1011.6 |
| 9°    | 980.3  |
| 10°   | 946.9  |
| 11°   | 908.1  |
| 12°   | 868.3  |
| 13°   | 828.4  |
| 14°   | 788.6  |
| 15°   | 746.5  |
| 17.5° | 647.4  |
| 20°   | 558.0  |
| 22.5° | 477.2  |
| 25°   | 407.2  |
| 27.5° | 341.5  |
| 30°   | 281.2  |
| 32.5° | 226.2  |
| 35°   | 176.7  |
| 37.5° | 134.7  |
| 40°   | 100.2  |
| 42.5° | 73.3   |
| 45°   | 53.9   |
| 47.5° | 40.9   |
| 50°   | 31.2   |
| 52.5° | 25.9   |
| 55°   | 22.6   |
| 57.5° | 19.4   |
| 60°   | 17.2   |
| 62.5° | 14.0   |
| 65°   | 12.9   |
| 67.5° | 10.8   |
| 70°   | 8.6    |
| 72.5° | 7.5    |
| 75°   | 6.5    |
| 77.5° | 5.4    |
| 80°   | 3.2    |
| 82.5° | 2.2    |
| 85°   | 2.2    |
| 87.5° | 1.1    |



TEST NUMBER: P1287113

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)