

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287115

Luminaire Tested: P3AS13R259030D2WDE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287115
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259030D2WDE010 E3PHLD1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 864.0 lumens
Efficiency: N/A
Efficacy: 43.0 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287115
CATALOG NUMBER: P3AS13R259030D2WDE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1287115
 CATALOG NUMBER: P3AS13R259030D2WDE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	69	65	61	59
6	81	70	63	58	79	69	62	57	68	62	57	66	61	57	65	60	56	65	60	56	55
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	61	56	52	50
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	57	52	48	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	43	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225442
5°	213999
10°	185345
15°	150898
20°	119220
25°	95062
30°	77075
35°	62774
40°	52012
45°	43819
50°	37082
55°	32649
60°	28594
65°	24957
70°	21927
75°	18385
80°	13764
85°	7799

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43819 cd/sqm



TEST NUMBER: P1287115

CATALOG NUMBER: P3AS13R259030D2WDE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.3	10.2
10°-20°	184.3	21.3
20°-30°	181.7	21.0
30°-40°	147.9	17.1
40°-50°	109.7	12.7
50°-60°	76.6	8.9
60°-70°	48.0	5.6
70°-80°	23.1	2.7
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	454.3	52.6
0°-40°	602.1	69.7
0°-60°	788.5	91.3
0°-90°	864.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	864.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1028	
5°	972	88
15°	665	184
25°	393	182
35°	234	148
45°	141	110
55°	85	77
65°	48	48
75°	22	23
85°	3	4
90°	0	



TEST NUMBER: P1287115
CATALOG NUMBER: P3AS13R259030D2WDE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1028.1
2.5°	1014.1
5°	972.2
7.5°	908.5
10°	832.4
12.5°	748.5
15°	664.7
17.5°	582.4
20°	510.9
22.5°	448.8
25°	392.9
27.5°	344.8
30°	304.4
32.5°	267.1
35°	234.5
37.5°	206.5
40°	181.7
42.5°	160.0
45°	141.3
47.5°	124.2
50°	108.7
52.5°	96.3
55°	85.4
57.5°	74.5
60°	65.2
62.5°	55.9
65°	48.1
67.5°	40.4
70°	34.2
72.5°	28.0
75°	21.7
77.5°	15.5
80°	10.9
82.5°	6.2
85°	3.1
87.5°	1.6
90°	0.0

(END OF REPORT)