

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286445

Luminaire Tested: P3AS05R309030D2WDE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286445  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R309030D2WDE010 E3DLD1H  
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 407.0 lumens  
Efficiency: N/A  
Efficacy: 36.7 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286445  
CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1286445  
 CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	96155
5°	93991
10°	87418
15°	77776
20°	66902
25°	56665
30°	47045
35°	36888
40°	26450
45°	17335
50°	9893
55°	6499
60°	6140
65°	5707
70°	5129
75°	4660
80°	4420
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17335 cd/sqm



TEST NUMBER: P1286445

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.6	9.7
10°-20°	95.2	23.4
20°-30°	107.3	26.4
30°-40°	85.7	21.1
40°-50°	44.1	10.8
50°-60°	16.6	4.1
60°-70°	10.9	2.7
70°-80°	5.9	1.4
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.2	59.5
0°-40°	327.9	80.6
0°-60°	388.6	95.5
0°-90°	407.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	407.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	438	
5°	427	40
15°	343	95
25°	234	107
35°	138	86
45°	56	44
55°	17	17
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1286445  
CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	438.5
1°	438.5
2°	437.0
3°	434.5
4°	431.0
5°	427.0
6°	422.0
7°	415.5
8°	408.5
9°	400.5
10°	392.6
11°	383.6
12°	374.1
13°	364.1
14°	353.6
15°	342.6
17.5°	314.6
20°	286.7
22.5°	259.7
25°	234.2
27.5°	209.3
30°	185.8
32.5°	161.8
35°	137.8
37.5°	114.4
40°	92.4
42.5°	72.9
45°	55.9
47.5°	41.5
50°	29.0
52.5°	20.5
55°	17.0
57.5°	15.5
60°	14.0
62.5°	12.5
65°	11.0
67.5°	9.5
70°	8.0
72.5°	6.5
75°	5.5
77.5°	4.5
80°	3.5
82.5°	2.5
85°	1.5
87.5°	0.5



TEST NUMBER: P1286445  
CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)