

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287127

Luminaire Tested: P3AS13R309030D2WDE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309030D2WDE010 E3D1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3D1WM TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1359.0 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287127

CATALOG NUMBER: P3AS13R309030D2WDE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287127

CATALOG NUMBER: P3AS13R309030D2WDE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97	96	95	94
3	108	103	100	97	106	102	99	96	99	97	95		97	95	93		95	93	92	90
4	105	99	95	92	103	98	95	92	96	93	91		94	92	90		93	91	89	88
5	101	96	92	89	100	95	91	88	93	90	87		92	89	87		90	88	86	85
6	99	92	88	85	97	92	88	85	90	87	85		89	86	84		88	85	83	82
7	96	89	85	82	95	89	85	82	88	84	82		87	84	81		86	83	81	80
8	93	87	83	80	92	86	82	80	85	82	79		84	81	79		84	81	79	78
9	91	84	80	77	90	84	80	77	83	79	77		82	79	77		82	79	77	76
10	88	82	78	75	88	81	78	75	81	77	75		80	77	75		80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1081251
5°	1067155
10°	931735
15°	592217
20°	234637
25°	78367
30°	36461
35°	16517
40°	6355
45°	3101
50°	887
55°	421
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3101 cd/sqm

TEST NUMBER: P1287127

CATALOG NUMBER: P3AS13R309030D2WDE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.3	32.6
10°-20°	687.4	50.6
20°-30°	177.2	13.0
30°-40°	41.6	3.1
40°-50°	8.1	0.6
50°-60°	0.9	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1307.9	96.2
0°-40°	1349.5	99.3
0°-60°	1358.5	100.0
0°-90°	1359.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1359.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4931	
5°	4848	443
15°	2609	687
25°	324	177
35°	62	42
45°	10	8
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1287127

CATALOG NUMBER: P3AS13R309030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4930.9
1°	4927.3
2°	4915.7
3°	4902.5
4°	4882.9
5°	4848.1
6°	4791.7
7°	4697.8
8°	4569.6
9°	4402.4
10°	4184.5
11°	3925.5
12°	3642.7
13°	3317.2
14°	2976.4
15°	2608.7
16°	2248.4
17°	1901.3
18°	1568.4
19°	1262.9
20°	1005.5
21°	791.3
22°	622.5
23°	492.7
24°	394.6
25°	323.9
26°	270.1
27°	229.5
28°	198.4
29°	169.9
30°	144.0
32.5°	90.7
35°	61.7
37.5°	38.5
40°	22.2
42.5°	14.8
45°	10.0
47.5°	5.8
50°	2.6
52.5°	1.1
55°	1.1
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P1287127

CATALOG NUMBER: P3AS13R309030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)