

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286458

Luminaire Tested: P3AS05R309030D2WDE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309030D2WDE010 E3PHLP1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 281.0 lumens
Efficiency: N/A
Efficacy: 25.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286458

CATALOG NUMBER: P3AS05R309030D2WDE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1286458

CATALOG NUMBER: P3AS05R309030D2WDE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	88	78	72	67	86	77	71	66	76	70	66		74	69	65		72
6	83	73	67	62	82	72	66	62	71	65	61		69	64	61		68
7	79	69	62	58	78	68	62	57	67	61	57		66	60	57		64
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	58	52	48	57	51	48		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91243
5°	86022
10°	73546
15°	58933
20°	45947
25°	34550
30°	25194
35°	17748
40°	12166
45°	8714
50°	7130
55°	6881
60°	6973
65°	7108
70°	7373
75°	7964
80°	8208
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 9744 cd/sqm

TEST NUMBER: P1286458

CATALOG NUMBER: P3AS05R309030D2WDE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.4	12.6
10°-20°	72.1	25.7
20°-30°	65.7	23.4
30°-40°	41.8	14.9
40°-50°	22.4	8.0
50°-60°	16.4	5.8
60°-70°	13.7	4.9
70°-80°	9.6	3.4
80°-90°	3.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.2	61.6
0°-40°	215.0	76.5
0°-60°	253.8	90.3
0°-90°	281.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	281.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	416	
5°	391	35
15°	260	72
25°	143	66
35°	66	42
45°	28	22
55°	18	16
65°	14	14
75°	9	10
85°	4	4
90°	0	

TEST NUMBER: P1286458

CATALOG NUMBER: P3AS05R309030D2WDE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	416.1
2.5°	409.6
5°	390.8
7.5°	363.4
10°	330.3
12.5°	294.9
15°	259.6
17.5°	227.1
20°	196.9
22.5°	168.7
25°	142.8
27.5°	119.7
30°	99.5
32.5°	80.8
35°	66.3
37.5°	52.6
40°	42.5
42.5°	33.9
45°	28.1
47.5°	23.1
50°	20.9
52.5°	19.5
55°	18.0
57.5°	17.3
60°	15.9
62.5°	15.1
65°	13.7
67.5°	13.0
70°	11.5
72.5°	10.1
75°	9.4
77.5°	7.9
80°	6.5
82.5°	5.8
85°	3.6
87.5°	1.4
90°	0.0

(END OF REPORT)