

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287148

Luminaire Tested: P3AS13R309030D2WDE010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1287148  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R309030D2WDE010 E3PHLP1MW  
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 605.0 lumens  
Efficiency: N/A  
Efficacy: 30.1 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287148  
CATALOG NUMBER: P3AS13R309030D2WDE010 E3PHLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1287148  
 CATALOG NUMBER: P3AS13R309030D2WDE010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68	68	68
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59	59	59	59
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	196432
5°	185230
10°	158336
15°	126879
20°	98895
25°	74375
30°	54236
35°	38226
40°	26221
45°	18762
50°	15351
55°	14833
60°	14999
65°	15306
70°	15900
75°	17114
80°	17679
85°	19625

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 20832 cd/sqm



TEST NUMBER: P1287148

CATALOG NUMBER: P3AS13R309030D2WDE010 E3PHLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.1	12.6
10°-20°	155.3	25.7
20°-30°	141.5	23.4
30°-40°	90.0	14.9
40°-50°	48.2	8.0
50°-60°	35.3	5.8
60°-70°	29.6	4.9
70°-80°	20.7	3.4
80°-90°	8.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.9	61.6
0°-40°	463.0	76.5
0°-60°	546.4	90.3
0°-90°	605.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	605.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	896	
5°	842	76
15°	559	155
25°	307	141
35°	143	90
45°	60	48
55°	39	35
65°	30	30
75°	20	21
85°	8	8
90°	0	



TEST NUMBER: P1287148  
CATALOG NUMBER: P3AS13R309030D2WDE010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	895.8
2.5°	881.8
5°	841.5
7.5°	782.5
10°	711.1
12.5°	635.0
15°	558.9
17.5°	489.0
20°	423.8
22.5°	363.3
25°	307.4
27.5°	257.7
30°	214.2
32.5°	173.9
35°	142.8
37.5°	113.3
40°	91.6
42.5°	73.0
45°	60.5
47.5°	49.7
50°	45.0
52.5°	41.9
55°	38.8
57.5°	37.3
60°	34.2
62.5°	32.6
65°	29.5
67.5°	27.9
70°	24.8
72.5°	21.7
75°	20.2
77.5°	17.1
80°	14.0
82.5°	12.4
85°	7.8
87.5°	3.1
90°	0.0

(END OF REPORT)