

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286471

Luminaire Tested: P3AS05R359030D2WDE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359030D2WDE010 E3DL1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 525.0 lumens
Efficiency: N/A
Efficacy: 47.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286471

CATALOG NUMBER: P3AS05R359030D2WDE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286471

CATALOG NUMBER: P3AS05R359030D2WDE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	264781
5°	254479
10°	221728
15°	169831
20°	113620
25°	68762
30°	39449
35°	22058
40°	11736
45°	6047
50°	2900
55°	2294
60°	2193
65°	1816
70°	1923
75°	1694
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6047 cd/sqm

TEST NUMBER: P1286471

CATALOG NUMBER: P3AS05R359030D2WDE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.2	20.0
10°-20°	203.8	38.8
20°-30°	133.4	25.4
30°-40°	54.1	10.3
40°-50°	16.3	3.1
50°-60°	5.5	1.1
60°-70°	3.7	0.7
70°-80°	2.2	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	442.5	84.3
0°-40°	496.6	94.6
0°-60°	518.4	98.7
0°-90°	525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1208	
5°	1156	105
15°	748	204
25°	284	133
35°	82	54
45°	20	16
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1286471

CATALOG NUMBER: P3AS05R359030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1207.5
1°	1205.5
2°	1200.0
3°	1189.0
4°	1176.1
5°	1156.1
6°	1131.1
7°	1103.2
8°	1071.7
9°	1035.7
10°	995.8
11°	951.3
12°	904.9
13°	853.0
14°	803.5
15°	748.1
17.5°	613.8
20°	486.9
22.5°	374.5
25°	284.2
27.5°	211.7
30°	155.8
32.5°	114.4
35°	82.4
37.5°	58.4
40°	41.0
42.5°	28.5
45°	19.5
47.5°	13.0
50°	8.5
52.5°	6.5
55°	6.0
57.5°	5.5
60°	5.0
62.5°	4.5
65°	3.5
67.5°	3.0
70°	3.0
72.5°	2.5
75°	2.0
77.5°	1.5
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5



TEST NUMBER: P1286471

CATALOG NUMBER: P3AS05R359030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)