

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287172

Luminaire Tested: P3AS13R359030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287172
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1131.1 lumens
Efficiency: N/A
Efficacy: 56.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287172
CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1287172
 CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	570437
5°	548205
10°	477658
15°	365859
20°	244765
25°	148097
30°	85000
35°	47515
40°	25247
45°	13025
50°	6243
55°	4932
60°	4736
65°	3891
70°	4167
75°	3643
80°	4041
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13025 cd/sqm



TEST NUMBER: P1287172

CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.6	20.0
10°-20°	439.1	38.8
20°-30°	287.5	25.4
30°-40°	116.6	10.3
40°-50°	35.0	3.1
50°-60°	11.9	1.1
60°-70°	8.0	0.7
70°-80°	4.7	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	953.2	84.3
0°-40°	1069.9	94.6
0°-60°	1116.8	98.7
0°-90°	1131.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1131.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2601	
5°	2490	227
15°	1612	439
25°	612	287
35°	178	117
45°	42	35
55°	13	12
65°	8	8
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1287172
CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2601.4
1°	2597.1
2°	2585.2
3°	2561.6
4°	2533.6
5°	2490.5
6°	2436.8
7°	2376.5
8°	2308.7
9°	2231.3
10°	2145.2
11°	2049.5
12°	1949.4
13°	1837.5
14°	1731.0
15°	1611.6
17.5°	1322.2
20°	1048.9
22.5°	806.9
25°	612.1
27.5°	456.2
30°	335.7
32.5°	246.4
35°	177.5
37.5°	125.9
40°	88.2
42.5°	61.3
45°	42.0
47.5°	28.0
50°	18.3
52.5°	14.0
55°	12.9
57.5°	11.8
60°	10.8
62.5°	9.7
65°	7.5
67.5°	6.5
70°	6.5
72.5°	5.4
75°	4.3
77.5°	3.2
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1



TEST NUMBER: P1287172
CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)