

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287173

Luminaire Tested: P3AS13R359030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359030D2WDE010 E3DLP1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 697.9 lumens
Efficiency: N/A
Efficacy: 34.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287173

CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287173

CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	224346
5°	218820
10°	200063
15°	169808
20°	134435
25°	101667
30°	74011
35°	50058
40°	30772
45°	17676
50°	10644
55°	8640
60°	7543
65°	6693
70°	5514
75°	5422
80°	5430
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17676 cd/sqm

TEST NUMBER: P1287173

CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.9	13.2
10°-20°	206.2	29.5
20°-30°	192.9	27.6
30°-40°	118.1	16.9
40°-50°	46.6	6.7
50°-60°	20.5	2.9
60°-70°	12.7	1.8
70°-80°	6.8	1.0
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.0	70.3
0°-40°	609.1	87.3
0°-60°	676.1	96.9
0°-90°	697.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	697.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1023	
5°	994	92
15°	748	206
25°	420	193
35°	187	118
45°	57	47
55°	23	20
65°	13	13
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1287173

CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1023.1
1°	1024.2
2°	1021.0
3°	1014.5
4°	1004.9
5°	994.1
6°	980.2
7°	964.0
8°	944.7
9°	923.2
10°	898.5
11°	872.7
12°	844.7
13°	814.6
14°	781.3
15°	748.0
17.5°	662.0
20°	576.1
22.5°	493.3
25°	420.2
27.5°	352.5
30°	292.3
32.5°	236.4
35°	187.0
37.5°	142.9
40°	107.5
42.5°	77.4
45°	57.0
47.5°	40.8
50°	31.2
52.5°	25.8
55°	22.6
57.5°	19.3
60°	17.2
62.5°	15.0
65°	12.9
67.5°	10.7
70°	8.6
72.5°	7.5
75°	6.4
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.1
87.5°	1.1



TEST NUMBER: P1287173

CATALOG NUMBER: P3AS13R359030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)