

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286506

Luminaire Tested: P3AS05R409030D2WDE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409030D2WDE010 E3DLD1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 446.1 lumens
Efficiency: N/A
Efficacy: 40.2 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286506

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1286506

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100124
5°	98305
10°	92673
15°	84155
20°	73950
25°	63149
30°	52312
35°	40341
40°	28711
45°	19351
50°	10541
55°	7455
60°	7017
65°	6486
70°	5770
75°	5507
80°	4420
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19351 cd/sqm

TEST NUMBER: P1286506

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.7	9.3
10°-20°	103.3	23.2
20°-30°	119.4	26.8
30°-40°	94.1	21.1
40°-50°	48.3	10.8
50°-60°	18.5	4.1
60°-70°	12.2	2.7
70°-80°	6.7	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	264.3	59.3
0°-40°	358.4	80.3
0°-60°	425.2	95.3
0°-90°	446.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	446.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	457	
5°	447	42
15°	371	103
25°	261	119
35°	151	94
45°	62	48
55°	20	18
65°	12	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1286506

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	456.6
2.5°	454.1
5°	446.6
7.5°	433.6
10°	416.2
12.5°	395.7
15°	370.7
17.5°	344.8
20°	316.9
22.5°	288.4
25°	261.0
27.5°	233.5
30°	206.6
32.5°	179.1
35°	150.7
37.5°	124.2
40°	100.3
42.5°	79.8
45°	62.4
47.5°	45.4
50°	30.9
52.5°	22.5
55°	19.5
57.5°	17.5
60°	16.0
62.5°	14.0
65°	12.5
67.5°	10.5
70°	9.0
72.5°	7.5
75°	6.5
77.5°	5.0
80°	3.5
82.5°	3.0
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)