

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287194

Luminaire Tested: P3AS13R409030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 471.1 lumens
Efficiency: N/A
Efficacy: 23.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287194

CATALOG NUMBER: P3AS13R409030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1287194

CATALOG NUMBER: P3AS13R409030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105737
5°	103808
10°	97861
15°	88877
20°	78080
25°	66681
30°	55249
35°	42590
40°	30314
45°	20436
50°	11155
55°	7875
60°	7412
65°	6849
70°	6091
75°	5846
80°	4672
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20436 cd/sqm

TEST NUMBER: P1287194

CATALOG NUMBER: P3AS13R409030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	9.3
10°-20°	109.1	23.2
20°-30°	126.1	26.8
30°-40°	99.4	21.1
40°-50°	51.0	10.8
50°-60°	19.5	4.1
60°-70°	12.9	2.7
70°-80°	7.0	1.5
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.1	59.3
0°-40°	378.5	80.3
0°-60°	449.0	95.3
0°-90°	471.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	471.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	482	
5°	472	44
15°	392	109
25°	276	126
35°	159	99
45°	66	51
55°	21	20
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1287194

CATALOG NUMBER: P3AS13R409030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	482.2
2.5°	479.5
5°	471.6
7.5°	457.9
10°	439.5
12.5°	417.9
15°	391.5
17.5°	364.1
20°	334.6
22.5°	304.6
25°	275.6
27.5°	246.6
30°	218.2
32.5°	189.2
35°	159.1
37.5°	131.2
40°	105.9
42.5°	84.3
45°	65.9
47.5°	48.0
50°	32.7
52.5°	23.7
55°	20.6
57.5°	18.4
60°	16.9
62.5°	14.8
65°	13.2
67.5°	11.1
70°	9.5
72.5°	7.9
75°	6.9
77.5°	5.3
80°	3.7
82.5°	3.2
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)