

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286513

Luminaire Tested: P3AS05R409030D2WDE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409030D2WDE010 E3DLP1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 367.0 lumens
Efficiency: N/A
Efficacy: 33.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286513

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1286513

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114267
5°	111952
10°	104251
15°	90852
20°	73226
25°	54874
30°	38588
35°	25270
40°	15314
45°	9148
50°	5458
55°	4396
60°	3947
65°	3373
70°	3206
75°	2542
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9148 cd/sqm

TEST NUMBER: P1286513

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.2	12.9
10°-20°	110.2	30.0
20°-30°	103.9	28.3
30°-40°	60.1	16.4
40°-50°	24.0	6.5
50°-60°	10.6	2.9
60°-70°	6.6	1.8
70°-80°	3.4	0.9
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.3	71.2
0°-40°	321.4	87.6
0°-60°	356.0	97.0
0°-90°	367.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	367.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	521	
5°	509	47
15°	400	110
25°	227	104
35°	94	60
45°	30	24
55°	12	11
65°	6	7
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1286513

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	521.1
2.5°	518.1
5°	508.6
7.5°	491.2
10°	468.2
12.5°	437.2
15°	400.2
17.5°	358.8
20°	313.8
22.5°	268.8
25°	226.8
27.5°	187.9
30°	152.4
32.5°	121.4
35°	94.4
37.5°	71.5
40°	53.5
42.5°	40.0
45°	29.5
47.5°	21.5
50°	16.0
52.5°	13.0
55°	11.5
57.5°	10.5
60°	9.0
62.5°	7.5
65°	6.5
67.5°	5.5
70°	5.0
72.5°	4.0
75°	3.0
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)