

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287215

Luminaire Tested: P3AS13R459030D2WDE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459030D2WDE010 E3DL1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1204.1 lumens
Efficiency: N/A
Efficacy: 59.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287215
CATALOG NUMBER: P3AS13R459030D2WDE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1287215
 CATALOG NUMBER: P3AS13R459030D2WDE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70			70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62			62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	452135
5°	441557
10°	405893
15°	343929
20°	266840
25°	186519
30°	117512
35°	69172
40°	39130
45°	19041
50°	6618
55°	5352
60°	5175
65°	5033
70°	4809
75°	4575
80°	4041
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19041 cd/sqm



TEST NUMBER: P1287215
 CATALOG NUMBER: P3AS13R459030D2WDE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.7	15.4
10°-20°	416.0	34.6
20°-30°	353.3	29.3
30°-40°	168.5	14.0
40°-50°	50.8	4.2
50°-60°	12.9	1.1
60°-70°	9.6	0.8
70°-80°	5.7	0.5
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	955.0	79.3
0°-40°	1123.5	93.3
0°-60°	1187.2	98.6
0°-90°	1204.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1204.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2062	
5°	2006	186
15°	1515	416
25°	771	353
35°	258	169
45°	61	51
55°	14	13
65°	10	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1287215
CATALOG NUMBER: P3AS13R459030D2WDE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2061.9
2.5°	2049.0
5°	2006.0
7.5°	1931.7
10°	1822.9
12.5°	1678.6
15°	1515.0
17.5°	1333.0
20°	1143.5
22.5°	950.8
25°	770.9
27.5°	607.3
30°	464.1
32.5°	348.9
35°	258.4
37.5°	190.6
40°	136.7
42.5°	94.8
45°	61.4
47.5°	34.5
50°	19.4
52.5°	15.1
55°	14.0
57.5°	12.9
60°	11.8
62.5°	10.8
65°	9.7
67.5°	8.6
70°	7.5
72.5°	6.5
75°	5.4
77.5°	4.3
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)