

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286538

Luminaire Tested: P3AS05R459030D2WDE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459030D2WDE010 E3DLP1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 360.0 lumens
Efficiency: N/A
Efficacy: 32.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286538

CATALOG NUMBER: P3AS05R459030D2WDE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1286538

CATALOG NUMBER: P3AS05R459030D2WDE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	62	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107228
5°	104776
10°	96658
15°	84041
20°	69049
25°	53713
30°	39677
35°	27920
40°	17433
45°	9427
50°	5117
55°	4396
60°	3947
65°	3373
70°	2885
75°	2965
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9427 cd/sqm

TEST NUMBER: P1286538

CATALOG NUMBER: P3AS05R459030D2WDE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	12.2
10°-20°	102.4	28.4
20°-30°	101.6	28.2
30°-40°	65.4	18.2
40°-50°	25.2	7.0
50°-60°	10.3	2.9
60°-70°	6.5	1.8
70°-80°	3.5	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	248.0	68.9
0°-40°	313.5	87.1
0°-60°	349.0	96.9
0°-90°	360.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	360.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	489	
5°	476	44
15°	370	102
25°	222	102
35°	104	65
45°	30	25
55°	12	10
65°	6	6
75°	4	3
85°	1	1
90°	0	

TEST NUMBER: P1286538

CATALOG NUMBER: P3AS05R459030D2WDE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	489.0
2.5°	486.5
5°	476.0
7.5°	458.1
10°	434.1
12.5°	404.2
15°	370.2
17.5°	333.3
20°	295.9
22.5°	258.0
25°	222.0
27.5°	188.1
30°	156.7
32.5°	129.2
35°	104.3
37.5°	81.8
40°	60.9
42.5°	43.9
45°	30.4
47.5°	20.5
50°	15.0
52.5°	12.5
55°	11.5
57.5°	10.0
60°	9.0
62.5°	7.5
65°	6.5
67.5°	5.5
70°	4.5
72.5°	4.0
75°	3.5
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)