

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286558

Luminaire Tested: P3AS05R509030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 214.0 lumens
Efficiency: N/A
Efficacy: 19.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286558

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286558

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43483
5°	42857
10°	40948
15°	37934
20°	34093
25°	29953
30°	25472
35°	20666
40°	15515
45°	9986
50°	4742
55°	3747
60°	3552
65°	3321
70°	2949
75°	2711
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9986 cd/sqm

TEST NUMBER: P1286558

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	8.5
10°-20°	46.6	21.8
20°-30°	56.6	26.4
30°-40°	48.0	22.4
40°-50°	24.9	11.6
50°-60°	9.0	4.2
60°-70°	6.2	2.9
70°-80°	3.4	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	121.4	56.7
0°-40°	169.4	79.2
0°-60°	203.3	95.0
0°-90°	214.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	214.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	198	
5°	195	18
15°	167	47
25°	124	57
35°	77	48
45°	32	25
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1286558

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	198.3
2.5°	197.6
5°	194.7
7.5°	190.3
10°	183.9
12.5°	175.9
15°	167.1
17.5°	157.0
20°	146.1
22.5°	134.8
25°	123.8
27.5°	112.4
30°	100.6
32.5°	88.9
35°	77.2
37.5°	65.7
40°	54.2
42.5°	43.2
45°	32.2
47.5°	21.5
50°	13.9
52.5°	10.7
55°	9.8
57.5°	8.8
60°	8.1
62.5°	7.1
65°	6.4
67.5°	5.4
70°	4.6
72.5°	3.9
75°	3.2
77.5°	2.4
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)