

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287241

Luminaire Tested: P3AS13R509030D2WDE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287241
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509030D2WDE010 E3D1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3D1WM TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1495.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287241

CATALOG NUMBER: P3AS13R509030D2WDE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287241

CATALOG NUMBER: P3AS13R509030D2WDE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	522436
5°	508539
10°	485295
15°	439321
20°	380086
25°	311776
30°	179091
35°	55626
40°	14942
45°	5241
50°	1262
55°	421
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5241 cd/sqm

TEST NUMBER: P1287241

CATALOG NUMBER: P3AS13R509030D2WDE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.4	14.5
10°-20°	536.2	35.9
20°-30°	563.6	37.7
30°-40°	161.3	10.8
40°-50°	15.8	1.1
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1316.2	88.0
0°-40°	1477.5	98.8
0°-60°	1494.6	100.0
0°-90°	1495.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1495.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2382	
5°	2310	216
15°	1935	536
25°	1289	564
35°	208	161
45°	17	16
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1287241

CATALOG NUMBER: P3AS13R509030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2382.5
1°	2378.8
2°	2368.3
3°	2353.0
4°	2332.4
5°	2310.3
6°	2286.5
7°	2261.2
8°	2237.5
9°	2210.1
10°	2179.5
11°	2144.1
12°	2103.5
13°	2052.9
14°	1998.0
15°	1935.2
16°	1868.8
17°	1804.4
18°	1738.5
19°	1680.5
20°	1628.8
21°	1579.2
22°	1522.8
23°	1457.9
24°	1381.9
25°	1288.6
26°	1187.3
27°	1074.4
28°	962.1
29°	840.8
30°	707.3
31°	582.3
32°	467.3
32.5°	417.2
33°	366.6
34°	281.1
35°	207.8
36°	152.4
37°	113.4
37.5°	98.1
38°	84.9
39°	65.9
40°	52.2
42.5°	29.5
45°	16.9



TEST NUMBER: P1287241

CATALOG NUMBER: P3AS13R509030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	9.5
50°	3.7
52.5°	1.6
55°	1.1
57.5°	1.1
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)