

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286563

Luminaire Tested: P3AS05R509030D2WDE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509030D2WDE010 E3DLD1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 437.1 lumens
Efficiency: N/A
Efficacy: 39.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286563

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286563

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88809
5°	87497
10°	83632
15°	77458
20°	69609
25°	61189
30°	52033
35°	42188
40°	31688
45°	20405
50°	9688
55°	7646
60°	7236
65°	6745
70°	6091
75°	5507
80°	5051
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20405 cd/sqm

TEST NUMBER: P1286563

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.3	8.5
10°-20°	95.1	21.8
20°-30°	115.6	26.4
30°-40°	98.0	22.4
40°-50°	50.9	11.6
50°-60°	18.4	4.2
60°-70°	12.7	2.9
70°-80°	6.9	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	247.9	56.7
0°-40°	345.9	79.2
0°-60°	415.2	95.0
0°-90°	437.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	437.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	405	
5°	398	37
15°	341	95
25°	253	116
35°	158	98
45°	66	51
55°	20	18
65°	13	13
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1286563

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	405.0
2.5°	403.5
5°	397.5
7.5°	388.5
10°	375.6
12.5°	359.1
15°	341.2
17.5°	320.7
20°	298.3
22.5°	275.3
25°	252.9
27.5°	229.4
30°	205.5
32.5°	181.5
35°	157.6
37.5°	134.2
40°	110.7
42.5°	88.3
45°	65.8
47.5°	43.9
50°	28.4
52.5°	21.9
55°	20.0
57.5°	18.0
60°	16.5
62.5°	14.5
65°	13.0
67.5°	11.0
70°	9.5
72.5°	8.0
75°	6.5
77.5°	5.0
80°	4.0
82.5°	3.0
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)