

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286564

Luminaire Tested: P3AS05R509030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509030D2WDE010 E3DLP1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 180.9 lumens
Efficiency: N/A
Efficacy: 16.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286564

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286564

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		0			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	113	110	107	105		111	108	106	103		104	102	100		100	99	97		97	95	94	93
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87	85
3	101	95	89	85		99	93	88	85		91	87	83		88	85	82		86	83	81	79
4	96	88	83	78		94	87	82	78		85	80	77		83	79	76		81	78	75	73
5	91	83	77	72		90	82	76	72		80	75	71		78	74	70		77	73	70	68
6	87	77	71	67		85	77	71	67		75	70	66		74	69	66		72	68	65	64
7	82	73	67	62		81	72	66	62		71	66	62		70	65	61		69	64	61	60
8	78	69	63	58		77	68	62	58		67	62	58		66	61	58		65	61	57	56
9	75	65	59	55		74	64	59	55		63	58	55		63	58	54		62	57	54	53
10	71	62	56	52		70	61	55	52		60	55	51		59	55	51		59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52649
5°	51222
10°	47227
15°	41544
20°	34746
25°	27558
30°	20231
35°	13893
40°	8845
45°	4931
50°	2661
55°	2256
60°	1930
65°	1764
70°	1539
75°	1440
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4931 cd/sqm

TEST NUMBER: P1286564

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.6	11.9
10°-20°	50.7	28.0
20°-30°	51.8	28.6
30°-40°	32.9	18.2
40°-50°	13.1	7.2
50°-60°	5.3	2.9
60°-70°	3.4	1.9
70°-80°	1.7	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	124.1	68.6
0°-40°	157.0	86.7
0°-60°	175.3	96.9
0°-90°	180.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	180.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	240	
5°	233	22
15°	183	51
25°	114	52
35°	52	33
45°	16	13
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1286564

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	240.1
2.5°	238.4
5°	232.7
7.5°	223.9
10°	212.1
12.5°	198.2
15°	183.0
17.5°	166.3
20°	148.9
22.5°	131.5
25°	113.9
27.5°	96.3
30°	79.9
32.5°	65.2
35°	51.9
37.5°	40.7
40°	30.9
42.5°	22.8
45°	15.9
47.5°	10.8
50°	7.8
52.5°	6.6
55°	5.9
57.5°	5.1
60°	4.4
62.5°	3.9
65°	3.4
67.5°	2.9
70°	2.4
72.5°	2.0
75°	1.7
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)