

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287306

Luminaire Tested: P3AS13R609030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 435.0 lumens
Efficiency: N/A
Efficacy: 21.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287306
CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1287306
 CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77209
5°	76359
10°	73702
15°	69626
20°	64196
25°	58116
30°	51603
35°	44089
40°	35066
45°	24716
50°	14771
55°	7455
60°	7192
65°	6590
70°	6091
75°	5846
80°	5304
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24716 cd/sqm



TEST NUMBER: P1287306

CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.6	7.5
10°-20°	85.7	19.7
20°-30°	110.1	25.3
30°-40°	102.1	23.5
40°-50°	62.1	14.3
50°-60°	20.7	4.8
60°-70°	12.6	2.9
70°-80°	7.1	1.6
80°-90°	2.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.4	52.5
0°-40°	330.4	76.0
0°-60°	413.3	95.0
0°-90°	435.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	435.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	352	
5°	347	33
15°	307	86
25°	240	110
35°	165	102
45°	80	62
55°	20	21
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1287306
CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	352.1
2.5°	350.6
5°	346.9
7.5°	340.0
10°	331.0
12.5°	319.9
15°	306.7
17.5°	291.4
20°	275.1
22.5°	257.6
25°	240.2
27.5°	222.3
30°	203.8
32.5°	185.3
35°	164.7
37.5°	143.1
40°	122.5
42.5°	100.8
45°	79.7
47.5°	61.8
50°	43.3
52.5°	25.9
55°	19.5
57.5°	18.0
60°	16.4
62.5°	14.3
65°	12.7
67.5°	11.1
70°	9.5
72.5°	7.9
75°	6.9
77.5°	5.3
80°	4.2
82.5°	2.6
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)