

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287316

Luminaire Tested: P3AS13R609030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1133.0 lumens
Efficiency: N/A
Efficacy: 56.4 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287316

CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1287316

CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		67
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	267544
5°	265000
10°	257288
15°	241046
20°	213332
25°	178462
30°	139870
35°	101482
40°	67498
45°	42082
50°	22788
55°	6576
60°	6140
65°	5604
70°	5514
75°	5507
80°	5430
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42082 cd/sqm

TEST NUMBER: P1287316

CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.4	10.0
10°-20°	294.6	26.0
20°-30°	335.7	29.6
30°-40°	238.1	21.0
40°-50°	108.0	9.5
50°-60°	22.9	2.0
60°-70°	11.1	1.0
70°-80°	6.8	0.6
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	743.7	65.6
0°-40°	981.8	86.7
0°-60°	1112.8	98.2
0°-90°	1133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1220	
5°	1204	113
15°	1062	295
25°	738	336
35°	379	238
45°	136	108
55°	17	23
65°	11	11
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1287316

CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1220.1
2.5°	1215.8
5°	1203.9
7.5°	1183.5
10°	1155.5
12.5°	1115.6
15°	1061.8
17.5°	993.9
20°	914.2
22.5°	828.1
25°	737.6
27.5°	645.0
30°	552.4
32.5°	464.1
35°	379.1
37.5°	303.7
40°	235.8
42.5°	178.8
45°	135.7
47.5°	101.2
50°	66.8
52.5°	31.2
55°	17.2
57.5°	15.1
60°	14.0
62.5°	12.9
65°	10.8
67.5°	9.7
70°	8.6
72.5°	7.5
75°	6.5
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)