

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286621

Luminaire Tested: P3AS05R609030D2WDE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609030D2WDE010 E3DLD1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 411.1 lumens
Efficiency: N/A
Efficacy: 37.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286621

CATALOG NUMBER: P3AS05R609030D2WDE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286621

CATALOG NUMBER: P3AS05R609030D2WDE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72955
5°	72133
10°	69649
15°	65789
20°	60649
25°	54923
30°	48742
35°	41653
40°	33119
45°	23351
50°	13953
55°	7073
60°	6798
65°	6226
70°	5770
75°	5507
80°	5051
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23351 cd/sqm

TEST NUMBER: P1286621

CATALOG NUMBER: P3AS05R609030D2WDE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.8	7.5
10°-20°	81.0	19.7
20°-30°	104.0	25.3
30°-40°	96.4	23.5
40°-50°	58.7	14.3
50°-60°	19.6	4.8
60°-70°	11.9	2.9
70°-80°	6.7	1.6
80°-90°	1.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	215.8	52.5
0°-40°	312.2	76.0
0°-60°	390.5	95.0
0°-90°	411.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	411.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	333	
5°	328	31
15°	290	81
25°	227	104
35°	156	96
45°	75	59
55°	18	20
65°	12	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1286621

CATALOG NUMBER: P3AS05R609030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	332.7
2.5°	331.2
5°	327.7
7.5°	321.2
10°	312.8
12.5°	302.3
15°	289.8
17.5°	275.4
20°	259.9
22.5°	243.4
25°	227.0
27.5°	210.0
30°	192.5
32.5°	175.1
35°	155.6
37.5°	135.2
40°	115.7
42.5°	95.3
45°	75.3
47.5°	58.4
50°	40.9
52.5°	24.4
55°	18.5
57.5°	17.0
60°	15.5
62.5°	13.5
65°	12.0
67.5°	10.5
70°	9.0
72.5°	7.5
75°	6.5
77.5°	5.0
80°	4.0
82.5°	2.5
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)