

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287334

Luminaire Tested: P3AS13R659030D2WDE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659030D2WDE010 E3DL1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1080.0 lumens
Efficiency: N/A
Efficacy: 53.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287334
CATALOG NUMBER: P3AS13R659030D2WDE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1287334
 CATALOG NUMBER: P3AS13R659030D2WDE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	254695
5°	251639
10°	242080
15°	226789
20°	203974
25°	173187
30°	135464
35°	96530
40°	63176
45°	39043
50°	19820
55°	6996
60°	6140
65°	6123
70°	5514
75°	5507
80°	5430
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 39043 cd/sqm



TEST NUMBER: P1287334

CATALOG NUMBER: P3AS13R659030D2WDE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.3	9.9
10°-20°	278.0	25.7
20°-30°	324.9	30.1
30°-40°	227.1	21.0
40°-50°	99.9	9.3
50°-60°	22.2	2.1
60°-70°	11.3	1.0
70°-80°	6.8	0.6
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	710.3	65.8
0°-40°	937.3	86.8
0°-60°	1059.5	98.1
0°-90°	1080.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1080.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1162	
5°	1143	107
15°	999	278
25°	716	325
35°	361	227
45°	126	100
55°	18	22
65°	12	11
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1287334

CATALOG NUMBER: P3AS13R659030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1161.5
2.5°	1157.2
5°	1143.2
7.5°	1119.5
10°	1087.2
12.5°	1047.4
15°	999.0
17.5°	939.8
20°	874.1
22.5°	799.8
25°	715.8
27.5°	627.6
30°	535.0
32.5°	445.7
35°	360.6
37.5°	286.3
40°	220.7
42.5°	166.9
45°	125.9
47.5°	92.6
50°	58.1
52.5°	30.1
55°	18.3
57.5°	16.1
60°	14.0
62.5°	12.9
65°	11.8
67.5°	9.7
70°	8.6
72.5°	7.5
75°	6.5
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)