

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286622

Luminaire Tested: P3AS05R609030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609030D2WDE010 E3DLP1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 178.0 lumens
Efficiency: N/A
Efficacy: 16.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286622
CATALOG NUMBER: P3AS05R609030D2WDE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1286622
 CATALOG NUMBER: P3AS05R609030D2WDE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45106
5°	44090
10°	41282
15°	37049
20°	31853
25°	26348
30°	20813
35°	15446
40°	10649
45°	6667
50°	3684
55°	2141
60°	1930
65°	1660
70°	1410
75°	1440
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6667 cd/sqm



TEST NUMBER: P1286622

CATALOG NUMBER: P3AS05R609030D2WDE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.7	10.5
10°-20°	45.3	25.5
20°-30°	49.7	27.9
30°-40°	36.2	20.3
40°-50°	17.1	9.6
50°-60°	5.6	3.1
60°-70°	3.2	1.8
70°-80°	1.7	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	113.7	63.9
0°-40°	149.9	84.2
0°-60°	172.6	97.0
0°-90°	178.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	178.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	206	
5°	200	19
15°	163	45
25°	109	50
35°	58	36
45°	22	17
55°	6	6
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1286622
CATALOG NUMBER: P3AS05R609030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	205.7
2.5°	204.5
5°	200.3
7.5°	194.0
10°	185.4
12.5°	175.1
15°	163.2
17.5°	150.2
20°	136.5
22.5°	122.6
25°	108.9
27.5°	95.2
30°	82.2
32.5°	69.7
35°	57.7
37.5°	47.0
40°	37.2
42.5°	28.6
45°	21.5
47.5°	15.7
50°	10.8
52.5°	7.1
55°	5.6
57.5°	4.9
60°	4.4
62.5°	3.7
65°	3.2
67.5°	2.7
70°	2.2
72.5°	2.0
75°	1.7
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)