

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287340

Luminaire Tested: P3AS13R659030D2WDE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659030D2WDE010 E3DLD1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 848.0 lumens
Efficiency: N/A
Efficacy: 42.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287340

CATALOG NUMBER: P3AS13R659030D2WDE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287340

CATALOG NUMBER: P3AS13R659030D2WDE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150909
5°	148866
10°	143885
15°	135687
20°	125148
25°	113619
30°	100623
35°	85635
40°	68128
45°	48098
50°	27905
55°	15216
60°	14166
65°	12868
70°	11733
75°	10929
80°	9471
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 48098 cd/sqm

TEST NUMBER: P1287340

CATALOG NUMBER: P3AS13R659030D2WDE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.6	7.5
10°-20°	167.2	19.7
20°-30°	214.9	25.3
30°-40°	198.8	23.4
40°-50°	120.0	14.2
50°-60°	40.9	4.8
60°-70°	24.6	2.9
70°-80°	13.9	1.6
80°-90°	4.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.7	52.6
0°-40°	644.5	76.0
0°-60°	805.5	95.0
0°-90°	848.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	848.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	688	
5°	676	64
15°	598	167
25°	470	215
35°	320	199
45°	155	120
55°	40	41
65°	25	25
75°	13	14
85°	3	4
90°	0	

TEST NUMBER: P1287340

CATALOG NUMBER: P3AS13R659030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	688.2
2.5°	685.0
5°	676.3
7.5°	663.4
10°	646.2
12.5°	624.6
15°	597.7
17.5°	568.6
20°	536.3
22.5°	502.9
25°	469.6
27.5°	434.0
30°	397.4
32.5°	360.8
35°	319.9
37.5°	280.0
40°	238.0
42.5°	196.0
45°	155.1
47.5°	117.4
50°	81.8
52.5°	51.7
55°	39.8
57.5°	35.5
60°	32.3
62.5°	28.0
65°	24.8
67.5°	21.5
70°	18.3
72.5°	16.2
75°	12.9
77.5°	10.8
80°	7.5
82.5°	5.4
85°	3.2
87.5°	2.2
90°	0.0

(END OF REPORT)