

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286635

Luminaire Tested: P3AS05R659030D2WDE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659030D2WDE010 E3D1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 595.0 lumens
Efficiency: N/A
Efficacy: 53.6 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286635
CATALOG NUMBER: P3AS05R659030D2WDE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1286635
 CATALOG NUMBER: P3AS05R659030D2WDE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159439
5°	148030
10°	143150
15°	137958
20°	127551
25°	116208
30°	89786
35°	52039
40°	20639
45°	8807
50°	2081
55°	268
60°	219
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8807 cd/sqm



TEST NUMBER: P1286635
 CATALOG NUMBER: P3AS05R659030D2WDE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.4	10.7
10°-20°	169.3	28.5
20°-30°	214.3	36.0
30°-40°	122.1	20.5
40°-50°	24.2	4.1
50°-60°	1.2	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	447.1	75.1
0°-40°	569.1	95.7
0°-60°	594.6	99.9
0°-90°	595.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	595.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	727	
5°	672	63
15°	608	169
25°	480	214
35°	194	122
45°	28	24
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1286635
CATALOG NUMBER: P3AS05R659030D2WDE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	727.1
1°	721.7
2°	710.0
3°	696.3
4°	682.8
5°	672.5
6°	665.0
7°	658.8
8°	653.5
9°	648.1
10°	642.9
11°	637.3
12°	631.5
13°	624.4
14°	616.8
15°	607.7
16°	597.0
17°	585.2
18°	572.5
19°	559.1
20°	546.6
21°	533.9
22°	522.4
23°	510.4
24°	496.5
25°	480.3
26°	461.0
27°	437.8
28°	411.6
29°	383.7
30°	354.6
31°	322.6
32°	290.8
32.5°	274.4
33°	258.5
34°	226.2
35°	194.4
36°	165.1
37°	136.0
37.5°	121.1
38°	109.1
39°	88.3
40°	72.1
42.5°	44.5
45°	28.4



TEST NUMBER: P1286635
CATALOG NUMBER: P3AS05R659030D2WDE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	16.6
50°	6.1
52.5°	1.2
55°	0.7
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)