

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287357

Luminaire Tested: P3AS13R709030D2WDE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709030D2WDE010 E3D1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3D1WN TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1284.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287357

CATALOG NUMBER: P3AS13R709030D2WDE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287357

CATALOG NUMBER: P3AS13R709030D2WDE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	81	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	249673
5°	235417
10°	223220
15°	219207
20°	211302
25°	199173
30°	197752
35°	172233
40°	111409
45°	52657
50°	7369
55°	612
60°	482
65°	571
70°	321
75°	424
80°	631
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 52657 cd/sqm

TEST NUMBER: P1287357

CATALOG NUMBER: P3AS13R709030D2WDE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	7.8
10°-20°	271.2	21.1
20°-30°	383.6	29.9
30°-40°	385.5	30.0
40°-50°	138.6	10.8
50°-60°	3.7	0.3
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.6	58.8
0°-40°	1140.2	88.8
0°-60°	1282.5	99.9
0°-90°	1284.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1284.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1139	
5°	1070	100
15°	966	271
25°	823	384
35°	643	386
45°	170	139
55°	2	4
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1287357

CATALOG NUMBER: P3AS13R709030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1138.6
1°	1135.4
2°	1125.4
3°	1109.6
4°	1089.5
5°	1069.5
6°	1050.5
7°	1035.7
8°	1022.5
9°	1012.0
10°	1002.5
11°	994.6
12°	987.2
13°	979.8
14°	973.0
15°	965.6
16°	956.6
17°	947.1
18°	935.5
19°	921.3
20°	905.5
21°	888.1
22°	870.7
23°	853.8
24°	837.4
25°	823.2
26°	813.2
27°	805.3
28°	798.9
29°	791.6
30°	781.0
31°	765.7
32°	744.1
32.5°	732.0
33°	715.6
34°	683.5
35°	643.4
36°	599.1
37°	549.0
37.5°	525.8
38°	494.1
39°	437.7
40°	389.2
42.5°	269.5
45°	169.8



TEST NUMBER: P1287357

CATALOG NUMBER: P3AS13R709030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	91.2
50°	21.6
52.5°	2.6
55°	1.6
57.5°	1.6
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)