

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286644

Luminaire Tested: P3AS05R659030D2WDE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659030D2WDE010 E3DL1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 501.0 lumens
Efficiency: N/A
Efficacy: 45.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286644

CATALOG NUMBER: P3AS05R659030D2WDE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286644

CATALOG NUMBER: P3AS05R659030D2WDE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118148
5°	116729
10°	112311
15°	105199
20°	94625
25°	80351
30°	62845
35°	44785
40°	29312
45°	18110
50°	9211
55°	3250
60°	2851
65°	2854
70°	2565
75°	2542
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18110 cd/sqm

TEST NUMBER: P1286644

CATALOG NUMBER: P3AS05R659030D2WDE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.8	9.9
10°-20°	129.0	25.7
20°-30°	150.7	30.1
30°-40°	105.3	21.0
40°-50°	46.4	9.3
50°-60°	10.3	2.1
60°-70°	5.3	1.0
70°-80°	3.2	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	329.5	65.8
0°-40°	434.8	86.8
0°-60°	491.5	98.1
0°-90°	501.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	501.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	539	
5°	530	50
15°	463	129
25°	332	151
35°	167	105
45°	58	46
55°	8	10
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1286644

CATALOG NUMBER: P3AS05R659030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	538.8
2.5°	536.8
5°	530.3
7.5°	519.3
10°	504.4
12.5°	485.9
15°	463.4
17.5°	435.9
20°	405.5
22.5°	371.0
25°	332.1
27.5°	291.1
30°	248.2
32.5°	206.7
35°	167.3
37.5°	132.8
40°	102.4
42.5°	77.4
45°	58.4
47.5°	42.9
50°	27.0
52.5°	14.0
55°	8.5
57.5°	7.5
60°	6.5
62.5°	6.0
65°	5.5
67.5°	4.5
70°	4.0
72.5°	3.5
75°	3.0
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)