

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287366

Luminaire Tested: P3AS13R709030D2WDE010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1287366  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R709030D2WDE010 E3DLP1LI  
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,  
E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 774.0 lumens  
Efficiency: N/A  
Efficacy: 38.5 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287366  
CATALOG NUMBER: P3AS13R709030D2WDE010 E3DLP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1287366  
 CATALOG NUMBER: P3AS13R709030D2WDE010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	181542
5°	178208
10°	168044
15°	152509
20°	133408
25°	112531
30°	92141
35°	71474
40°	51153
45°	32375
50°	16170
55°	9863
60°	8508
65°	7835
70°	6924
75°	6354
80°	5430
85°	5535

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 32375 cd/sqm



TEST NUMBER: P1287366

CATALOG NUMBER: P3AS13R709030D2WDE010 E3DLP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.5	9.8
10°-20°	186.9	24.2
20°-30°	212.9	27.5
30°-40°	166.5	21.5
40°-50°	81.8	10.6
50°-60°	25.1	3.2
60°-70°	14.9	1.9
70°-80°	8.0	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	475.4	61.4
0°-40°	641.9	82.9
0°-60°	748.8	96.7
0°-90°	774.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	774.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	828	
5°	810	76
15°	672	187
25°	465	213
35°	267	166
45°	104	82
55°	26	25
65°	15	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1287366

CATALOG NUMBER: P3AS13R709030D2WDE010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	827.9
2.5°	823.6
5°	809.6
7.5°	787.0
10°	754.7
12.5°	717.0
15°	671.8
17.5°	623.4
20°	571.7
22.5°	517.9
25°	465.1
27.5°	413.4
30°	363.9
32.5°	314.4
35°	267.0
37.5°	221.8
40°	178.7
42.5°	138.9
45°	104.4
47.5°	73.2
50°	47.4
52.5°	31.2
55°	25.8
57.5°	22.6
60°	19.4
62.5°	17.2
65°	15.1
67.5°	12.9
70°	10.8
72.5°	8.6
75°	7.5
77.5°	6.5
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)