

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286679

Luminaire Tested: P3AS05R709030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709030D2WDE010 E3DLP1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 359.0 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286679

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286679

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84204
5°	82654
10°	77954
15°	70738
20°	61885
25°	52188
30°	42741
35°	33140
40°	23730
45°	15009
50°	7505
55°	4588
60°	3947
65°	3632
70°	3206
75°	2965
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15009 cd/sqm

TEST NUMBER: P1286679

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.0	9.8
10°-20°	86.7	24.1
20°-30°	98.8	27.5
30°-40°	77.2	21.5
40°-50°	37.9	10.6
50°-60°	11.7	3.3
60°-70°	6.9	1.9
70°-80°	3.7	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	220.5	61.4
0°-40°	297.7	82.9
0°-60°	347.3	96.7
0°-90°	359.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	359.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	384	
5°	376	35
15°	312	87
25°	216	99
35°	124	77
45°	48	38
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1286679

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	384.0
2.5°	382.0
5°	375.5
7.5°	365.0
10°	350.1
12.5°	332.6
15°	311.6
17.5°	289.1
20°	265.2
22.5°	240.2
25°	215.7
27.5°	191.8
30°	168.8
32.5°	145.8
35°	123.8
37.5°	102.9
40°	82.9
42.5°	64.4
45°	48.4
47.5°	34.0
50°	22.0
52.5°	14.5
55°	12.0
57.5°	10.5
60°	9.0
62.5°	8.0
65°	7.0
67.5°	6.0
70°	5.0
72.5°	4.0
75°	3.5
77.5°	3.0
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)