

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286690

Luminaire Tested: P3AS09R159030D2WDE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286690
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159030D2WDE010 E3D1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 846.0 lumens
Efficiency: N/A
Efficacy: 57.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286690

CATALOG NUMBER: P3AS09R159030D2WDE010 E3D1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1286690

CATALOG NUMBER: P3AS09R159030D2WDE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96		
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94		
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	92		
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91		
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89		
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88		
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86		
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86	85		
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	84		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1644430
5°	1378183
10°	649175
15°	195711
20°	72410
25°	28163
30°	10508
35°	3212
40°	1145
45°	620
50°	443
55°	497
60°	570
65°	363
70°	449
75°	593
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 620 cd/sqm

TEST NUMBER: P1286690

CATALOG NUMBER: P3AS09R159030D2WDE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	484.0	57.2
10°-20°	287.7	34.0
20°-30°	60.4	7.1
30°-40°	9.7	1.2
40°-50°	1.6	0.2
50°-60°	1.2	0.1
60°-70°	0.8	0.1
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	832.2	98.4
0°-40°	842.0	99.5
0°-60°	844.8	99.9
0°-90°	846.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	846.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7499	
5°	6261	484
15°	862	288
25°	116	60
35°	12	10
45°	2	2
55°	1	1
65°	1	1
75°	1	0
85°	0	0
90°	0	

TEST NUMBER: P1286690

CATALOG NUMBER: P3AS09R159030D2WDE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7499.2
1°	7475.8
2°	7356.7
3°	7118.6
4°	6769.4
5°	6261.1
6°	5663.8
7°	4980.9
8°	4328.8
9°	3590.4
10°	2915.5
12.5°	1573.1
15°	862.1
17.5°	505.0
20°	310.3
22.5°	190.0
25°	116.4
27.5°	70.2
30°	41.5
32.5°	23.4
35°	12.0
37.5°	6.7
40°	4.0
42.5°	2.7
45°	2.0
47.5°	1.3
50°	1.3
52.5°	1.3
55°	1.3
57.5°	1.3
60°	1.3
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)