

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287406

Luminaire Tested: P3AS17R209030D2WDE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209030D2WDE010 E3CB1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3CB1M
TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1819.0 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287406
CATALOG NUMBER: P3AS17R209030D2WDE010 E3CB1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1287406
 CATALOG NUMBER: P3AS17R209030D2WDE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	99	98	98	98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	97	96	95	93
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	96	94	92	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	94	92	91	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	93	90	89	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	91	89	87	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	89	87	85	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	88	86	84	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	87	84	82	87	84	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2825125
5°	2452096
10°	1515136
15°	526246
20°	161621
25°	57124
30°	21142
35°	8486
40°	4523
45°	1799
50°	989
55°	1109
60°	1272
65°	726
70°	898
75°	1186
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1799 cd/sqm



TEST NUMBER: P1287406

CATALOG NUMBER: P3AS17R209030D2WDE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	924.5	50.8
10°-20°	733.6	40.3
20°-30°	127.0	7.0
30°-40°	23.1	1.3
40°-50°	5.3	0.3
50°-60°	2.6	0.1
60°-70°	1.6	0.1
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1785.1	98.1
0°-40°	1808.2	99.4
0°-60°	1816.1	99.8
0°-90°	1819.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1819.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12884	
5°	11140	925
15°	2318	734
25°	236	127
35°	32	23
45°	6	5
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1287406
CATALOG NUMBER: P3AS17R209030D2WDE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	12883.6
1°	12821.6
2°	12576.9
3°	12183.8
4°	11723.1
5°	11139.9
6°	10471.8
7°	9694.3
8°	8808.8
9°	7813.9
10°	6804.6
12.5°	4292.1
15°	2318.1
17.5°	1238.2
20°	692.6
22.5°	396.0
25°	236.1
27.5°	144.0
30°	83.5
32.5°	49.0
35°	31.7
37.5°	21.6
40°	15.8
42.5°	10.1
45°	5.8
47.5°	2.9
50°	2.9
52.5°	2.9
55°	2.9
57.5°	2.9
60°	2.9
62.5°	1.4
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)