

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286692

Luminaire Tested: P3AS09R159030D2WDE010 E3D1WMH

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1286692  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R159030D2WDE010 E3D1WMH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3D1WM TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 865.0 lumens  
Efficiency: N/A  
Efficacy: 58.8 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286692

CATALOG NUMBER: P3AS09R159030D2WDE010 E3D1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1286692

CATALOG NUMBER: P3AS09R159030D2WDE010 E3D1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 |  | 104 | 103 | 102 |  | 101 |
| 2   | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 |  | 102 | 100 | 99  |  | 99  |
| 3   | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99  | 102 | 100 | 98  |  | 100 | 98  | 96  |  | 98  |
| 4   | 107 | 102 | 99  | 96  | 106 | 101 | 98  | 96  | 99  | 97  | 95  |  | 98  | 96  | 94  |  | 96  |
| 5   | 105 | 100 | 96  | 94  | 103 | 99  | 96  | 93  | 97  | 94  | 92  |  | 96  | 93  | 92  |  | 94  |
| 6   | 102 | 97  | 94  | 91  | 101 | 96  | 93  | 91  | 95  | 92  | 90  |  | 94  | 92  | 90  |  | 93  |
| 7   | 100 | 95  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 88  |  | 92  | 90  | 88  |  | 91  |
| 8   | 98  | 93  | 89  | 87  | 97  | 92  | 89  | 87  | 91  | 89  | 87  |  | 91  | 88  | 86  |  | 90  |
| 9   | 96  | 91  | 88  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  |  | 89  | 87  | 85  |  | 89  |
| 10  | 95  | 89  | 86  | 84  | 94  | 89  | 86  | 84  | 88  | 85  | 83  |  | 88  | 85  | 83  |  | 87  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1647193 |
| 5°  | 1343162 |
| 10° | 657815  |
| 15° | 201341  |
| 20° | 85267   |
| 25° | 38567   |
| 30° | 15040   |
| 35° | 6933    |
| 40° | 2147    |
| 45° | 806     |
| 50° | 341     |
| 55° | 115     |
| 60° | 132     |
| 65° | 156     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 806 cd/sqm

TEST NUMBER: P1286692

CATALOG NUMBER: P3AS09R159030D2WDE010 E3D1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 475.0  | 54.9      |
| 10°-20°   | 291.5  | 33.7      |
| 20°-30°   | 78.3   | 9.1       |
| 30°-40°   | 17.2   | 2.0       |
| 40°-50°   | 2.4    | 0.3       |
| 50°-60°   | 0.4    | 0.0       |
| 60°-70°   | 0.2    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 844.7  | 97.7      |
| 0°-40°    | 861.9  | 99.7      |
| 0°-60°    | 864.8  | 100.0     |
| 0°-90°    | 865.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 865.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 7512 |      |
| 5°  | 6102 | 475  |
| 15° | 887  | 291  |
| 25° | 159  | 78   |
| 35° | 26   | 17   |
| 45° | 3    | 2    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1286692

CATALOG NUMBER: P3AS09R159030D2WDE010 E3D1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 7511.8 |
| 1°    | 7464.9 |
| 2°    | 7314.3 |
| 3°    | 7043.1 |
| 4°    | 6634.7 |
| 5°    | 6102.0 |
| 6°    | 5499.5 |
| 7°    | 4828.4 |
| 8°    | 4211.8 |
| 9°    | 3558.1 |
| 10°   | 2954.3 |
| 11°   | 2356.6 |
| 12°   | 1813.2 |
| 13°   | 1394.6 |
| 14°   | 1104.0 |
| 15°   | 886.9  |
| 17.5° | 549.7  |
| 20°   | 365.4  |
| 22.5° | 246.0  |
| 25°   | 159.4  |
| 27.5° | 94.5   |
| 30°   | 59.4   |
| 32.5° | 40.0   |
| 35°   | 25.9   |
| 37.5° | 14.4   |
| 40°   | 7.5    |
| 42.5° | 4.3    |
| 45°   | 2.6    |
| 47.5° | 1.6    |
| 50°   | 1.0    |
| 52.5° | 0.7    |
| 55°   | 0.3    |
| 57.5° | 0.3    |
| 60°   | 0.3    |
| 62.5° | 0.3    |
| 65°   | 0.3    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1286692

CATALOG NUMBER: P3AS09R159030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)