

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286704

Luminaire Tested: P3AS09R159030D2WDE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159030D2WDE010 E3DLD1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 528.0 lumens
Efficiency: N/A
Efficacy: 35.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286704

CATALOG NUMBER: P3AS09R159030D2WDE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286704

CATALOG NUMBER: P3AS09R159030D2WDE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133191
5°	129562
10°	118412
15°	103724
20°	88978
25°	74278
30°	59452
35°	44598
40°	32346
45°	21149
50°	13236
55°	8946
60°	7938
65°	7264
70°	6860
75°	6270
80°	5935
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21149 cd/sqm

TEST NUMBER: P1286704

CATALOG NUMBER: P3AS09R159030D2WDE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	10.3
10°-20°	127.3	24.1
20°-30°	140.2	26.6
30°-40°	105.0	19.9
40°-50°	54.4	10.3
50°-60°	22.6	4.3
60°-70°	14.0	2.6
70°-80°	7.9	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	321.9	61.0
0°-40°	426.9	80.9
0°-60°	503.9	95.4
0°-90°	528.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	607	
5°	589	54
15°	457	127
25°	307	140
35°	167	105
45°	68	54
55°	23	23
65°	14	14
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P1286704

CATALOG NUMBER: P3AS09R159030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	607.4
1°	608.0
2°	606.0
3°	602.0
4°	596.0
5°	588.6
6°	579.3
7°	569.2
8°	557.2
9°	544.5
10°	531.8
12.5°	495.0
15°	456.9
17.5°	418.7
20°	381.3
22.5°	343.1
25°	307.0
27.5°	270.9
30°	234.8
32.5°	199.3
35°	166.6
37.5°	138.5
40°	113.0
42.5°	89.6
45°	68.2
47.5°	51.5
50°	38.8
52.5°	28.8
55°	23.4
57.5°	20.7
60°	18.1
62.5°	16.1
65°	14.0
67.5°	12.0
70°	10.7
72.5°	8.7
75°	7.4
77.5°	6.0
80°	4.7
82.5°	3.3
85°	2.0
87.5°	0.7
90°	0.0

(END OF REPORT)