

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287446

Luminaire Tested: P3AS17R259030D2WDE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259030D2WDE010 E3DL1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1508.0 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287446

CATALOG NUMBER: P3AS17R259030D2WDE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287446

CATALOG NUMBER: P3AS17R259030D2WDE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	967335
5°	902507
10°	722966
15°	490741
20°	296942
25°	173647
30°	98901
35°	54395
40°	28883
45°	15195
50°	8836
55°	6614
60°	5701
65°	5967
70°	5514
75°	4914
80°	3662
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15195 cd/sqm

TEST NUMBER: P1287446

CATALOG NUMBER: P3AS17R259030D2WDE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.8	24.1
10°-20°	594.3	39.4
20°-30°	339.6	22.5
30°-40°	134.0	8.9
40°-50°	41.1	2.7
50°-60°	16.2	1.1
60°-70°	10.9	0.7
70°-80°	6.1	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1297.8	86.1
0°-40°	1431.8	94.9
0°-60°	1489.1	98.7
0°-90°	1508.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1508.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4411	
5°	4100	364
15°	2162	594
25°	718	340
35°	203	134
45°	49	41
55°	17	16
65°	12	11
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1287446

CATALOG NUMBER: P3AS17R259030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4411.4
1°	4402.7
2°	4366.7
3°	4303.3
4°	4215.4
5°	4100.1
6°	3964.6
7°	3811.8
8°	3634.6
9°	3453.0
10°	3246.9
11°	3043.7
12°	2820.3
13°	2599.8
14°	2373.6
15°	2161.7
17.5°	1676.1
20°	1272.5
22.5°	955.5
25°	717.7
27.5°	531.8
30°	390.6
32.5°	282.5
35°	203.2
37.5°	144.1
40°	100.9
42.5°	69.2
45°	49.0
47.5°	34.6
50°	25.9
52.5°	20.2
55°	17.3
57.5°	15.9
60°	13.0
62.5°	11.5
65°	11.5
67.5°	10.1
70°	8.6
72.5°	7.2
75°	5.8
77.5°	4.3
80°	2.9
82.5°	2.9
85°	1.4
87.5°	1.4



TEST NUMBER: P1287446

CATALOG NUMBER: P3AS17R259030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)