

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286707

Luminaire Tested: P3AS09R159030D2WDE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286707
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159030D2WDE010 E3DLP1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 412.0 lumens
Efficiency: N/A
Efficacy: 28.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286707
CATALOG NUMBER: P3AS09R159030D2WDE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1286707
 CATALOG NUMBER: P3AS09R159030D2WDE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177661
5°	164208
10°	131104
15°	99024
20°	75397
25°	57463
30°	41171
35°	26876
40°	16459
45°	9955
50°	6618
55°	5123
60°	4386
65°	3840
70°	3462
75°	3389
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9955 cd/sqm



TEST NUMBER: P1286707

CATALOG NUMBER: P3AS09R159030D2WDE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.1	16.0
10°-20°	121.9	29.6
20°-30°	108.6	26.3
30°-40°	64.2	15.6
40°-50°	26.4	6.4
50°-60°	12.4	3.0
60°-70°	7.5	1.8
70°-80°	4.0	1.0
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.6	72.0
0°-40°	360.8	87.6
0°-60°	399.5	97.0
0°-90°	412.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	412.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	810	
5°	746	66
15°	436	122
25°	238	109
35°	100	64
45°	32	26
55°	13	12
65°	7	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1286707
CATALOG NUMBER: P3AS09R159030D2WDE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	810.2
1°	808.2
2°	802.2
3°	790.1
4°	770.1
5°	746.0
6°	719.9
7°	689.1
8°	657.0
9°	624.2
10°	588.8
12.5°	507.8
15°	436.2
17.5°	374.7
20°	323.1
22.5°	277.7
25°	237.5
27.5°	198.7
30°	162.6
32.5°	129.8
35°	100.4
37.5°	76.9
40°	57.5
42.5°	42.8
45°	32.1
47.5°	24.8
50°	19.4
52.5°	16.1
55°	13.4
57.5°	11.4
60°	10.0
62.5°	8.7
65°	7.4
67.5°	6.7
70°	5.4
72.5°	4.7
75°	4.0
77.5°	2.7
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)