

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286739

Luminaire Tested: P3AS09R209030D2WDE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209030D2WDE010 E3PHLP1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 328.0 lumens
Efficiency: N/A
Efficacy: 22.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286739

CATALOG NUMBER: P3AS09R209030D2WDE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1286739

CATALOG NUMBER: P3AS09R209030D2WDE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	73	81	76	72		79	74	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	66		72
6	84	74	67	62	82	73	66	62	71	66	61		70	65	61		68
7	79	69	63	58	78	68	62	58	67	62	57		66	61	57		65
8	76	65	59	54	74	65	58	54	64	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	59	52	48	68	58	52	48	57	52	48		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116635
5°	108804
10°	90290
15°	69036
20°	51805
25°	39002
30°	28840
35°	20157
40°	13826
45°	9582
50°	8221
55°	8105
60°	8464
65°	8509
70°	8655
75°	8981
80°	9723
85°	9812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 11424 cd/sqm

TEST NUMBER: P1286739

CATALOG NUMBER: P3AS09R209030D2WDE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	13.5
10°-20°	84.6	25.8
20°-30°	74.4	22.7
30°-40°	48.0	14.6
40°-50°	25.4	7.8
50°-60°	19.1	5.8
60°-70°	16.2	5.0
70°-80°	11.5	3.5
80°-90°	4.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.2	62.0
0°-40°	251.2	76.6
0°-60°	295.8	90.2
0°-90°	328.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	328.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	532	
5°	494	44
15°	304	85
25°	161	74
35°	75	48
45°	31	25
55°	21	19
65°	16	16
75°	11	11
85°	4	4
90°	0	

TEST NUMBER: P1286739

CATALOG NUMBER: P3AS09R209030D2WDE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	531.9
2.5°	521.3
5°	494.3
7.5°	452.8
10°	405.5
12.5°	353.3
15°	304.1
17.5°	259.7
20°	222.0
22.5°	190.2
25°	161.2
27.5°	136.1
30°	113.9
32.5°	93.6
35°	75.3
37.5°	60.8
40°	48.3
42.5°	38.6
45°	30.9
47.5°	27.0
50°	24.1
52.5°	22.2
55°	21.2
57.5°	20.3
60°	19.3
62.5°	17.4
65°	16.4
67.5°	15.4
70°	13.5
72.5°	12.5
75°	10.6
77.5°	9.7
80°	7.7
82.5°	6.8
85°	3.9
87.5°	1.9
90°	0.0

(END OF REPORT)