

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287539

Luminaire Tested: P3AS17R409030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 631.0 lumens
Efficiency: N/A
Efficacy: 23.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287539
CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1287539

CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141655
5°	139071
10°	131104
15°	119070
20°	104612
25°	89328
30°	74011
35°	57072
40°	40619
45°	27352
50°	14942
55°	10513
60°	9911
65°	9132
70°	8142
75°	7795
80°	6188
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27352 cd/sqm



TEST NUMBER: P1287539

CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.9	9.3
10°-20°	146.1	23.2
20°-30°	168.9	26.8
30°-40°	133.1	21.1
40°-50°	68.3	10.8
50°-60°	26.1	4.1
60°-70°	17.3	2.7
70°-80°	9.4	1.5
80°-90°	2.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	373.9	59.3
0°-40°	507.1	80.4
0°-60°	601.5	95.3
0°-90°	631.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	631.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	646	
5°	632	59
15°	524	146
25°	369	169
35°	213	133
45°	88	68
55°	28	26
65°	18	17
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P1287539
CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	646.0
2.5°	642.4
5°	631.8
7.5°	613.5
10°	588.8
12.5°	559.8
15°	524.5
17.5°	487.8
20°	448.3
22.5°	408.0
25°	369.2
27.5°	330.4
30°	292.3
32.5°	253.4
35°	213.2
37.5°	175.8
40°	141.9
42.5°	113.0
45°	88.2
47.5°	64.2
50°	43.8
52.5°	31.8
55°	27.5
57.5°	24.7
60°	22.6
62.5°	19.8
65°	17.6
67.5°	14.8
70°	12.7
72.5°	10.6
75°	9.2
77.5°	7.1
80°	4.9
82.5°	4.2
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)