

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286762

Luminaire Tested: P3AS09R259030D2WDE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286762  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R259030D2WDE010 E3DLD1WMH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 537.0 lumens  
Efficiency: N/A  
Efficacy: 36.5 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286762  
CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1286762

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70				70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51				51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	127621
5°	124587
10°	115451
15°	102816
20°	88348
25°	75101
30°	61832
35°	48185
40°	34665
45°	21987
50°	12997
55°	8946
60°	8201
65°	7627
70°	6860
75°	6270
80°	5935
85°	5032

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21987 cd/sqm



TEST NUMBER: P1286762

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.5	9.8
10°-20°	125.7	23.4
20°-30°	142.1	26.5
30°-40°	112.4	20.9
40°-50°	56.8	10.6
50°-60°	22.7	4.2
60°-70°	14.5	2.7
70°-80°	8.0	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	320.3	59.6
0°-40°	432.7	80.6
0°-60°	512.1	95.4
0°-90°	537.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	582	
5°	566	52
15°	453	126
25°	310	142
35°	180	112
45°	71	57
55°	23	23
65°	15	15
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1286762  
CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	582.0
1°	582.0
2°	580.0
3°	576.7
4°	572.0
5°	566.0
6°	558.6
7°	549.9
8°	540.5
9°	529.8
10°	518.5
11°	505.8
12°	493.7
13°	479.7
14°	466.3
15°	452.9
17.5°	415.4
20°	378.6
22.5°	343.9
25°	310.4
27.5°	277.6
30°	244.2
32.5°	212.7
35°	180.0
37.5°	149.9
40°	121.1
42.5°	94.3
45°	70.9
47.5°	52.9
50°	38.1
52.5°	28.8
55°	23.4
57.5°	21.4
60°	18.7
62.5°	16.7
65°	14.7
67.5°	12.7
70°	10.7
72.5°	9.4
75°	7.4
77.5°	6.0
80°	4.7
82.5°	3.3
85°	2.0
87.5°	0.7



TEST NUMBER: P1286762  
CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)