

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287549

Luminaire Tested: P3AS17R409030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287549
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1678.0 lumens
Efficiency: N/A
Efficacy: 61.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287549
CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1287549

CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	742506
5°	720931
10°	654230
15°	540480
20°	389864
25°	241151
30°	130552
35°	67458
40°	36697
45°	20560
50°	10302
55°	7723
60°	6929
65°	6745
70°	6475
75°	6100
80°	5430
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20560 cd/sqm



TEST NUMBER: P1287549

CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.9	18.0
10°-20°	648.3	38.6
20°-30°	462.6	27.6
30°-40°	170.3	10.1
40°-50°	53.6	3.2
50°-60°	18.6	1.1
60°-70°	12.8	0.8
70°-80°	7.6	0.5
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1412.8	84.2
0°-40°	1583.1	94.3
0°-60°	1655.4	98.7
0°-90°	1678.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1678.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3386	
5°	3275	302
15°	2381	648
25°	997	463
35°	252	170
45°	66	54
55°	20	19
65°	13	13
75°	7	8
85°	1	2
90°	0	



TEST NUMBER: P1287549
CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3386.1
2.5°	3360.2
5°	3275.2
7.5°	3134.0
10°	2938.2
12.5°	2689.0
15°	2380.8
17.5°	2035.1
20°	1670.7
22.5°	1312.1
25°	996.7
27.5°	731.7
30°	515.6
32.5°	361.5
35°	252.0
37.5°	178.6
40°	128.2
42.5°	92.2
45°	66.3
47.5°	44.6
50°	30.2
52.5°	21.6
55°	20.2
57.5°	18.7
60°	15.8
62.5°	14.4
65°	13.0
67.5°	11.5
70°	10.1
72.5°	8.6
75°	7.2
77.5°	5.8
80°	4.3
82.5°	2.9
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)