

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287570

Luminaire Tested: P3AS17R459030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1287570  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R459030D2WDE010 E3DLP1GPH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 509.0 lumens  
Efficiency: N/A  
Efficacy: 18.6 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 27.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287570

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DLP1GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1287570

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 113 | 110 | 107 | 105 |  | 111 | 108 | 106 | 103 |  | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  | 96  | 94  |
| 2   | 107 | 102 | 98  | 94  |  | 105 | 100 | 96  | 93  |  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  | 89  | 87  |
| 3   | 102 | 95  | 90  | 85  |  | 100 | 93  | 89  | 85  |  | 91  | 87  | 83  |  | 88  | 85  | 82  |  | 86  | 83  | 81  |
| 4   | 96  | 88  | 83  | 78  |  | 94  | 87  | 82  | 78  |  | 85  | 81  | 77  |  | 83  | 79  | 76  |  | 81  | 78  | 75  |
| 5   | 91  | 83  | 77  | 72  |  | 90  | 82  | 76  | 72  |  | 80  | 75  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |
| 6   | 87  | 78  | 72  | 67  |  | 85  | 77  | 71  | 67  |  | 75  | 70  | 66  |  | 74  | 69  | 66  |  | 73  | 69  | 66  |
| 7   | 83  | 73  | 67  | 63  |  | 81  | 72  | 67  | 63  |  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 61  |
| 8   | 79  | 69  | 63  | 59  |  | 77  | 68  | 63  | 59  |  | 67  | 62  | 58  |  | 66  | 62  | 58  |  | 65  | 61  | 58  |
| 9   | 75  | 65  | 59  | 55  |  | 74  | 65  | 59  | 55  |  | 64  | 59  | 55  |  | 63  | 58  | 55  |  | 62  | 58  | 55  |
| 10  | 72  | 62  | 56  | 52  |  | 71  | 61  | 56  | 52  |  | 61  | 55  | 52  |  | 60  | 55  | 52  |  | 59  | 55  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 151611 |
| 5°  | 148162 |
| 10° | 136671 |
| 15° | 118843 |
| 20° | 97635  |
| 25° | 75972  |
| 30° | 56085  |
| 35° | 39485  |
| 40° | 24646  |
| 45° | 13335  |
| 50° | 7232   |
| 55° | 6193   |
| 60° | 5570   |
| 65° | 4774   |
| 70° | 4039   |
| 75° | 4151   |
| 80° | 3536   |
| 85° | 3522   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 13335 cd/sqm

TEST NUMBER: P1287570

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DLP1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 62.3   | 12.2      |
| 10°-20°   | 144.7  | 28.4      |
| 20°-30°   | 143.7  | 28.2      |
| 30°-40°   | 92.5   | 18.2      |
| 40°-50°   | 35.6   | 7.0       |
| 50°-60°   | 14.5   | 2.8       |
| 60°-70°   | 9.2    | 1.8       |
| 70°-80°   | 4.9    | 1.0       |
| 80°-90°   | 1.5    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 350.7  | 68.9      |
| 0°-40°    | 443.3  | 87.1      |
| 0°-60°    | 493.4  | 96.9      |
| 0°-90°    | 509.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 509.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 691 |      |
| 5°  | 673 | 62   |
| 15° | 524 | 145  |
| 25° | 314 | 144  |
| 35° | 148 | 93   |
| 45° | 43  | 36   |
| 55° | 16  | 14   |
| 65° | 9   | 9    |
| 75° | 5   | 5    |
| 85° | 1   | 2    |
| 90° | 0   |      |

TEST NUMBER: P1287570

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 691.4 |
| 2.5°  | 687.9 |
| 5°    | 673.1 |
| 7.5°  | 647.7 |
| 10°   | 613.8 |
| 12.5° | 571.5 |
| 15°   | 523.5 |
| 17.5° | 471.3 |
| 20°   | 418.4 |
| 22.5° | 364.7 |
| 25°   | 314.0 |
| 27.5° | 266.0 |
| 30°   | 221.5 |
| 32.5° | 182.7 |
| 35°   | 147.5 |
| 37.5° | 115.7 |
| 40°   | 86.1  |
| 42.5° | 62.1  |
| 45°   | 43.0  |
| 47.5° | 28.9  |
| 50°   | 21.2  |
| 52.5° | 17.6  |
| 55°   | 16.2  |
| 57.5° | 14.1  |
| 60°   | 12.7  |
| 62.5° | 10.6  |
| 65°   | 9.2   |
| 67.5° | 7.8   |
| 70°   | 6.3   |
| 72.5° | 5.6   |
| 75°   | 4.9   |
| 77.5° | 3.5   |
| 80°   | 2.8   |
| 82.5° | 2.1   |
| 85°   | 1.4   |
| 87.5° | 0.7   |
| 90°   | 0.0   |

(END OF REPORT)