

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286807

Luminaire Tested: P3AS09R359030D2WDE010 E3CD1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286807  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R359030D2WDE010 E3CD1MB  
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3CD1MI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 850.0 lumens  
Efficiency: N/A  
Efficacy: 57.8 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286807  
CATALOG NUMBER: P3AS09R359030D2WDE010 E3CD1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1286807  
 CATALOG NUMBER: P3AS09R359030D2WDE010 E3CD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	94	94	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	94	92	90	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	81	78	76	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	77	74	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	554254
5°	542966
10°	505134
15°	370331
20°	189623
25°	68351
30°	26612
35°	9316
40°	3836
45°	1023
50°	921
55°	1032
60°	877
65°	675
70°	833
75°	1101
80°	884
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 1176 cd/sqm



TEST NUMBER: P1286807

CATALOG NUMBER: P3AS09R359030D2WDE010 E3CD1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	230.0	27.1
10°-20°	431.5	50.8
20°-30°	152.8	18.0
30°-40°	26.7	3.1
40°-50°	3.9	0.5
50°-60°	2.2	0.3
60°-70°	1.5	0.2
70°-80°	1.1	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.2	95.8
0°-40°	840.9	98.9
0°-60°	847.0	99.7
0°-90°	850.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	850.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2528	
5°	2467	230
15°	1631	431
25°	282	153
35°	35	27
45°	3	4
55°	3	2
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1286807  
CATALOG NUMBER: P3AS09R359030D2WDE010 E3CD1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2527.6
1°	2526.9
2°	2518.9
3°	2503.5
4°	2489.5
5°	2466.7
6°	2443.3
7°	2417.2
8°	2385.0
9°	2334.8
10°	2268.6
11°	2176.9
12°	2066.4
13°	1935.2
14°	1790.6
15°	1631.3
17.5°	1214.9
20°	812.6
22.5°	490.0
25°	282.5
27.5°	168.7
30°	105.1
32.5°	60.9
35°	34.8
37.5°	22.1
40°	13.4
42.5°	6.7
45°	3.3
47.5°	2.7
50°	2.7
52.5°	2.7
55°	2.7
57.5°	2.0
60°	2.0
62.5°	2.0
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0



TEST NUMBER: P1286807  
CATALOG NUMBER: P3AS09R359030D2WDE010 E3CD1MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)