

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286827

Luminaire Tested: P3AS09R359030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 703.0 lumens
Efficiency: N/A
Efficacy: 47.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286827
CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1286827

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	354555
5°	340765
10°	296899
15°	227402
20°	152147
25°	92062
30°	52818
35°	29526
40°	15687
45°	8094
50°	3889
55°	3058
60°	2938
65°	2439
70°	2565
75°	2288
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8094 cd/sqm



TEST NUMBER: P1286827

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.9	20.0
10°-20°	272.9	38.8
20°-30°	178.7	25.4
30°-40°	72.5	10.3
40°-50°	21.8	3.1
50°-60°	7.4	1.1
60°-70°	5.0	0.7
70°-80°	2.9	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.5	84.3
0°-40°	665.0	94.6
0°-60°	694.1	98.7
0°-90°	703.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	703.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1617	
5°	1548	141
15°	1002	273
25°	380	179
35°	110	72
45°	26	22
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1286827
CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1616.9
1°	1614.3
2°	1606.9
3°	1592.2
4°	1574.8
5°	1548.1
6°	1514.6
7°	1477.2
8°	1435.0
9°	1386.9
10°	1333.4
11°	1273.9
12°	1211.7
13°	1142.2
14°	1076.0
15°	1001.7
17.5°	821.8
20°	652.0
22.5°	501.5
25°	380.5
27.5°	283.5
30°	208.6
32.5°	153.1
35°	110.3
37.5°	78.2
40°	54.8
42.5°	38.1
45°	26.1
47.5°	17.4
50°	11.4
52.5°	8.7
55°	8.0
57.5°	7.4
60°	6.7
62.5°	6.0
65°	4.7
67.5°	4.0
70°	4.0
72.5°	3.3
75°	2.7
77.5°	2.0
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.7



TEST NUMBER: P1286827
CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)