

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287619

Luminaire Tested: P3AS17R559030D2WDE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559030D2WDE010 E3DL1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DL1M
TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1570.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287619
CATALOG NUMBER: P3AS17R559030D2WDE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1287619
 CATALOG NUMBER: P3AS17R559030D2WDE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	431106
5°	426743
10°	412105
15°	380933
20°	328702
25°	259612
30°	184180
35°	118748
40°	71334
45°	40190
50°	21628
55°	7723
60°	6929
65°	6745
70°	6475
75°	6100
80°	5430
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 40190 cd/sqm



TEST NUMBER: P1287619

CATALOG NUMBER: P3AS17R559030D2WDE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.3	11.6
10°-20°	464.0	29.6
20°-30°	486.3	31.0
30°-40°	283.7	18.1
40°-50°	106.2	6.8
50°-60°	25.0	1.6
60°-70°	12.8	0.8
70°-80°	7.6	0.5
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1132.6	72.1
0°-40°	1416.3	90.2
0°-60°	1547.4	98.6
0°-90°	1570.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1570.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1966	
5°	1939	182
15°	1678	464
25°	1073	486
35°	444	284
45°	130	106
55°	20	25
65°	13	13
75°	7	8
85°	1	2
90°	0	



TEST NUMBER: P1287619
CATALOG NUMBER: P3AS17R559030D2WDE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1966.0
2.5°	1960.3
5°	1938.7
7.5°	1904.1
10°	1850.8
12.5°	1775.9
15°	1678.0
17.5°	1554.1
20°	1408.6
22.5°	1245.9
25°	1073.0
27.5°	895.9
30°	727.4
32.5°	574.7
35°	443.6
37.5°	337.0
40°	249.2
42.5°	178.6
45°	129.6
47.5°	93.6
50°	63.4
52.5°	36.0
55°	20.2
57.5°	17.3
60°	15.8
62.5°	14.4
65°	13.0
67.5°	11.5
70°	10.1
72.5°	8.6
75°	7.2
77.5°	5.8
80°	4.3
82.5°	2.9
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)