

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287660

Luminaire Tested: P3AS17R609030D2WDE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609030D2WDE010 E3DLP1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1047.0 lumens
Efficiency: N/A
Efficacy: 38.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287660
CATALOG NUMBER: P3AS17R609030D2WDE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1287660
 CATALOG NUMBER: P3AS17R609030D2WDE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265352
5°	259387
10°	242837
15°	217867
20°	187360
25°	154920
30°	122399
35°	90908
40°	62603
45°	39260
50°	21594
55°	12654
60°	11359
65°	9703
70°	8271
75°	8557
80°	7324
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 39260 cd/sqm



TEST NUMBER: P1287660

CATALOG NUMBER: P3AS17R609030D2WDE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.7	10.5
10°-20°	266.5	25.5
20°-30°	292.4	27.9
30°-40°	213.0	20.3
40°-50°	100.6	9.6
50°-60°	33.0	3.1
60°-70°	18.7	1.8
70°-80°	10.1	1.0
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	668.6	63.9
0°-40°	881.6	84.2
0°-60°	1015.2	97.0
0°-90°	1047.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1047.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1210	
5°	1178	110
15°	960	267
25°	640	292
35°	340	213
45°	127	101
55°	33	33
65°	19	19
75°	10	10
85°	3	3
90°	0	



TEST NUMBER: P1287660
CATALOG NUMBER: P3AS17R609030D2WDE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1210.1
2.5°	1202.9
5°	1178.4
7.5°	1141.0
10°	1090.6
12.5°	1030.2
15°	959.7
17.5°	883.4
20°	802.9
22.5°	720.9
25°	640.3
27.5°	559.7
30°	483.4
32.5°	410.1
35°	339.6
37.5°	276.3
40°	218.7
42.5°	168.3
45°	126.6
47.5°	92.1
50°	63.3
52.5°	41.7
55°	33.1
57.5°	28.8
60°	25.9
62.5°	21.6
65°	18.7
67.5°	15.8
70°	12.9
72.5°	11.5
75°	10.1
77.5°	7.2
80°	5.8
82.5°	4.3
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)