

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286884

Luminaire Tested: P3AS09R459030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286884
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 748.0 lumens
Efficiency: N/A
Efficacy: 50.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286884

CATALOG NUMBER: P3AS09R459030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1286884

CATALOG NUMBER: P3AS09R459030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	280899
5°	274311
10°	252166
15°	213668
20°	165774
25°	115894
30°	72999
35°	42965
40°	24331
45°	11815
50°	4094
55°	3326
60°	3245
65°	3113
70°	3013
75°	2796
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 11815 cd/sqm

TEST NUMBER: P1286884

CATALOG NUMBER: P3AS09R459030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	15.4
10°-20°	258.5	34.6
20°-30°	219.5	29.3
30°-40°	104.7	14.0
40°-50°	31.5	4.2
50°-60°	8.0	1.1
60°-70°	6.0	0.8
70°-80°	3.5	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	593.3	79.3
0°-40°	698.0	93.3
0°-60°	737.5	98.6
0°-90°	748.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	748.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1281	
5°	1246	115
15°	941	258
25°	479	219
35°	160	105
45°	38	32
55°	9	8
65°	6	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1286884

CATALOG NUMBER: P3AS09R459030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1281.0
2.5°	1273.0
5°	1246.2
7.5°	1200.1
10°	1132.5
12.5°	1042.9
15°	941.2
17.5°	828.1
20°	710.4
22.5°	590.7
25°	479.0
27.5°	377.3
30°	288.3
32.5°	216.7
35°	160.5
37.5°	118.4
40°	85.0
42.5°	58.9
45°	38.1
47.5°	21.4
50°	12.0
52.5°	9.4
55°	8.7
57.5°	8.0
60°	7.4
62.5°	6.7
65°	6.0
67.5°	5.4
70°	4.7
72.5°	4.0
75°	3.3
77.5°	2.7
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)