

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286885

Luminaire Tested: P3AS09R459030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459030D2WDE010 E3DLP1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 483.0 lumens
Efficiency: N/A
Efficacy: 32.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286885
CATALOG NUMBER: P3AS09R459030D2WDE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1286885
 CATALOG NUMBER: P3AS09R459030D2WDE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143870
5°	140590
10°	129679
15°	112782
20°	92641
25°	72077
30°	53223
35°	37450
40°	23387
45°	12652
50°	6857
55°	5887
60°	5307
65°	4514
70°	3847
75°	3982
80°	3410
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12652 cd/sqm



TEST NUMBER: P1286885

CATALOG NUMBER: P3AS09R459030D2WDE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.2	12.2
10°-20°	137.3	28.4
20°-30°	136.3	28.2
30°-40°	87.8	18.2
40°-50°	33.8	7.0
50°-60°	13.8	2.8
60°-70°	8.7	1.8
70°-80°	4.7	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.8	68.9
0°-40°	420.6	87.1
0°-60°	468.2	96.9
0°-90°	483.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	483.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	656	
5°	639	59
15°	497	137
25°	298	136
35°	140	88
45°	41	34
55°	15	14
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1286885
CATALOG NUMBER: P3AS09R459030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	656.1
2.5°	652.7
5°	638.7
7.5°	614.6
10°	582.4
12.5°	542.3
15°	496.8
17.5°	447.2
20°	397.0
22.5°	346.1
25°	297.9
27.5°	252.4
30°	210.2
32.5°	173.4
35°	139.9
37.5°	109.8
40°	81.7
42.5°	58.9
45°	40.8
47.5°	27.4
50°	20.1
52.5°	16.7
55°	15.4
57.5°	13.4
60°	12.1
62.5°	10.0
65°	8.7
67.5°	7.4
70°	6.0
72.5°	5.4
75°	4.7
77.5°	3.3
80°	2.7
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)