

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287708

Luminaire Tested: P3AS17R709030D2WDE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709030D2WDE010 E3DL1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1450.0 lumens
Efficiency: N/A
Efficacy: 53.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287708

CATALOG NUMBER: P3AS17R709030D2WDE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287708

CATALOG NUMBER: P3AS17R709030D2WDE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	280701
5°	277349
10°	269334
15°	257913
20°	241591
25°	219497
30°	189599
35°	151112
40°	110063
45°	72349
50°	33909
55°	10475
60°	10087
65°	9703
70°	9232
75°	9743
80°	9092
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 72349 cd/sqm

TEST NUMBER: P1287708

CATALOG NUMBER: P3AS17R709030D2WDE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.6	8.2
10°-20°	318.0	21.9
20°-30°	413.3	28.5
30°-40°	350.7	24.2
40°-50°	180.8	12.5
50°-60°	34.9	2.4
60°-70°	18.9	1.3
70°-80°	11.6	0.8
80°-90°	3.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	849.9	58.6
0°-40°	1200.6	82.8
0°-60°	1416.2	97.7
0°-90°	1450.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1450.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1280	
5°	1260	119
15°	1136	318
25°	907	413
35°	564	351
45°	233	181
55°	27	35
65°	19	19
75°	12	12
85°	3	3
90°	0	



TEST NUMBER: P1287708

CATALOG NUMBER: P3AS17R709030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1280.1
2.5°	1275.8
5°	1260.0
7.5°	1236.9
10°	1209.6
12.5°	1175.0
15°	1136.1
17.5°	1088.6
20°	1035.3
22.5°	974.9
25°	907.2
27.5°	830.9
30°	748.8
32.5°	658.1
35°	564.5
37.5°	472.3
40°	384.5
42.5°	302.4
45°	233.3
47.5°	171.4
50°	99.4
52.5°	43.2
55°	27.4
57.5°	25.9
60°	23.0
62.5°	21.6
65°	18.7
67.5°	17.3
70°	14.4
72.5°	13.0
75°	11.5
77.5°	8.6
80°	7.2
82.5°	4.3
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)