

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286928

Luminaire Tested: P3AS09R559030D2WDE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286928
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559030D2WDE010 E3DL1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 729.0 lumens
Efficiency: N/A
Efficacy: 49.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286928
CATALOG NUMBER: P3AS09R559030D2WDE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1286928
 CATALOG NUMBER: P3AS09R559030D2WDE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	200181
5°	198150
10°	191357
15°	176868
20°	152637
25°	120539
30°	85507
35°	55145
40°	33119
45°	18669
50°	10030
55°	3594
60°	3245
65°	3113
70°	3013
75°	2796
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18669 cd/sqm



TEST NUMBER: P1286928

CATALOG NUMBER: P3AS09R559030D2WDE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.7	11.6
10°-20°	215.4	29.6
20°-30°	225.8	31.0
30°-40°	131.7	18.1
40°-50°	49.3	6.8
50°-60°	11.6	1.6
60°-70°	6.0	0.8
70°-80°	3.5	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	525.9	72.1
0°-40°	657.6	90.2
0°-60°	718.5	98.6
0°-90°	729.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	729.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	913	
5°	900	85
15°	779	215
25°	498	226
35°	206	132
45°	60	49
55°	9	12
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1286928
CATALOG NUMBER: P3AS09R559030D2WDE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	912.9
2.5°	910.2
5°	900.2
7.5°	884.1
10°	859.4
12.5°	824.6
15°	779.1
17.5°	721.6
20°	654.1
22.5°	578.5
25°	498.2
27.5°	416.0
30°	337.7
32.5°	266.8
35°	206.0
37.5°	156.5
40°	115.7
42.5°	82.9
45°	60.2
47.5°	43.5
50°	29.4
52.5°	16.7
55°	9.4
57.5°	8.0
60°	7.4
62.5°	6.7
65°	6.0
67.5°	5.4
70°	4.7
72.5°	4.0
75°	3.3
77.5°	2.7
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)