

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286932

Luminaire Tested: P3AS09R559030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 278.0 lumens
Efficiency: N/A
Efficacy: 18.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286932

CATALOG NUMBER: P3AS09R559030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286932

CATALOG NUMBER: P3AS09R559030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52277
5°	51596
10°	49565
15°	46357
20°	42284
25°	37744
30°	33018
35°	27412
40°	21612
45°	14668
50°	8972
55°	4626
60°	4342
65°	4099
70°	3783
75°	3304
80°	3283
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14668 cd/sqm

TEST NUMBER: P1286932

CATALOG NUMBER: P3AS09R559030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.0	7.9
10°-20°	57.1	20.5
20°-30°	71.5	25.7
30°-40°	63.8	23.0
40°-50°	37.4	13.4
50°-60°	12.9	4.6
60°-70°	7.8	2.8
70°-80°	4.3	1.6
80°-90°	1.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	150.6	54.2
0°-40°	214.4	77.1
0°-60°	264.6	95.2
0°-90°	278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	278.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	238	
5°	234	22
15°	204	57
25°	156	71
35°	102	64
45°	47	37
55°	12	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1286932

CATALOG NUMBER: P3AS09R559030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	238.4
2.5°	237.1
5°	234.4
7.5°	229.2
10°	222.6
12.5°	214.4
15°	204.2
17.5°	193.4
20°	181.2
22.5°	168.8
25°	156.0
27.5°	143.2
30°	130.4
32.5°	116.6
35°	102.4
37.5°	88.7
40°	75.5
42.5°	61.4
45°	47.3
47.5°	36.1
50°	26.3
52.5°	17.1
55°	12.1
57.5°	10.8
60°	9.9
62.5°	8.9
65°	7.9
67.5°	6.9
70°	5.9
72.5°	4.9
75°	3.9
77.5°	3.3
80°	2.6
82.5°	1.6
85°	1.0
87.5°	0.7
90°	0.0

(END OF REPORT)